


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	NEW DRAWING	15DEC2020	KR	AM

CSJA
Cold Shrink "All-in-one" in-line joint



PART DESCRIPTION	VOLTAGE CLASS	L* INCHES (MM)	REQUIRED INSTALLATION SPACE INCHES (MM)
CSJA-1521	15kV	29 (737)	39 (990)
CSJA-1522	15kV	29 (737)	39 (990)
CSJA-1523	15kV	33 (838)	43 (1090)
CSJA-1524	15kV	37 (939)	49 (1244)
CSJA-2822	28kV	29 (737)	39 (990)
CSJA-2823	28kV	33 (838)	43 (1090)
CSJA-2824	28kV	37 (939)	49 (1244)
CSJA-3523	35kV	33 (838)	43 (1090)
CSJA-3524	35kV	37 (939)	49 (1244)
CSJA-3525	35kV	37 (939)	49 (1244)

*NOTE:

BASED ON ASBS MECHANICAL CONNECTORS QUALIFIED TO ANSI C119-4. INSTALLED LENGTH MAY VARY DEPENDING ON CABLE DIMENSIONS AND CABLE CONNECTOR TYPE USED.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA K 15DEC2020	TE Connectivity Ltd.	
		CHK C. RIVA 15DEC2020		
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME MEDIUM VOLTAGE COLD APPLIED JOINTS CSJA
MATERIAL		APVD C. RIVA 15DEC2020 PRODUCT SPEC APPLICATION SPEC		
FINISH		WEIGHT CUSTOMER DRAWING		SIZE A3 CAGE CODE 00779 DRAWING NO G-MV_CA_CSJA-AMS RESTRICTED TO -
		SCALE NTS		SHEET 1 of 1 REV 1