



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	INITIAL RELEASE	26AUG2021	GK	MN

### LABEL AND LINER DESIGN

### PRESENTATION



All dimensions in mm [Inches]

**TE PN: A41119-000**

**OUTSIDE WOUND  
LABEL ACROSS: 4  
PER ROLL QTY: 10000**

MATERIAL	NYLON CLOTH
ADHESIVE TYPE	PERMANENT ACRYLIC
LINER	GLASSINE PAPER

THIS DRAWING IS A CONTROLLED DOCUMENT.

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm [INCHES]	
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
ANGLES	± -
MATERIAL	FINISH
SEE TABLE	-

DWN	26AUG2021
GOPALAKRISHNA HV	
CHK	26AUG2021
MIKE NUTTALL	
APVD	26AUG2021
MIKE NUTTALL	
PRODUCT SPEC	
TTDS-051	
APPLICATION SPEC	
WEIGHT	0.225g

TE Connectivity			
NAME			
NC - NYLON CLOTH LABELS			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	C2290	C-NC-250381-10-9	-
CUSTOMER DRAWING		SCALE	SHEET
		NTS	1 OF 1
		REV	D