


REVISION			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE OF CD PER ECO-19-013153	9/18/2019	I. MYONG



NOTES:

- CHEMICAL AND HEAT RESISTANT EPOXY ADHESIVE.
- TEMPERATURE RANGE: -55°C TO +150°C
- BOXED KIT CONTENTS;

<p><u>KIT 1:</u> 5 ADHESIVE SACHETS, 10g EACH. 5 MIXING CUPS 5 ABRASIVE PAPER SHEETS 5 MIXING STICKS 1 INSTALLATION PROCEDURE</p> <p><u>KIT 8:</u> 1 50 ML DUAL SYRINGE, 2-25 ML BARRELS, WITH MIXING NOZZLES. 5 MIXING CUPS 5 ABRASIVE PAPER SHEETS 5 MIXING STICKS 1 INSTALLATION PROCEDURE</p>	<p><u>KIT 4:</u> 5 ADHESIVE SACHETS, 10g EACH</p> <p><u>KIT 5:</u> 1 ADHESIVE SACHET, 10g.</p>
---	--

4. SPECIFICATIONS:

RT-1011
RK-6619
DIN VG-95343
NASA SP-R-022A

5. SDS DOCUMENTS

RAY 3006
RAY 3006A
RAY 3006B

6. SHELF LIFE:

REFER TO TE SPEC
SHEET No. 126-116006.

Raychem Harness & Components **CUSTOMER DRAWING**

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. AND INCH DIMENSIONS ARE IN SHOWN IN (PARENTHESES).			
DECIMALS: .000 ± 0.000 .00 ± 0.00 .0 ± 0.0	ANGLES: ± 0° 00'		
TE CONNECTIVITY RESERVES THE RIGHT TO AMEND THIS DRAWING AT ANYTIME. USERS SHOULD EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION.		TITLE: TE/Raychem CHEMICAL AND HEAT-RESISTANT ADHESIVE	
		DRAWING NO: S1125	
DRAWN: 20Jun2019 G.Rositano	APPROVED: 19JUL2019 I.Myong	CAGE CODE 06090	CAD FILE: S1124_cd
SIZE: A	SCALE: 1/1	THIRD ANGLE PROJ. 	SHEET: 1_OF_1