



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	NEW DRAWING FORMAT	18MAR2017	GK	DB
	F	LINER CHANGE	10SEP2018	GK	DB

LABEL AND LINER DESIGN

PRESENTATION



**OUTSIDE WOUND LABEL ACROSS: 5
PER ROLL QTY: 10,000**

All dimensions in mm [Inch]

TE PN: CM9613-000

UL-MARKING AND LABELLING SYSTEMS		
PGIS2 - Marking and Labeling Systems, Limited Use - Component (UL 969)		
File: MH61871	Product design: SBP	Ribbon: TMS-XXX-RIBBON-4RPSCE

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm [INCHES]	
	0 PLC ±
	1 PLC ±
	2 PLC ±
	3 PLC ±
	4 PLC ±
	ANGLES ±
	FINISH ±
MATERIAL	GLOSSY
SEE TABLE	

MATERIAL	CLEAR VINYL
ADHESIVE TYPE	ACRYLIC PERMANENT
LINEAR	WHITE KRAFT
DWN	18MAR2017
CHK	GOPALAKRISHNA HV
APVD	18MAR2017
NAME	D.BURGAT
PRODUCT SPEC	TIDS-211
APPLICATION SPEC	
SIZE	A2
CAGE CODE	00779
DRAWING NO	SBP050100WE10
RESTRICTED TO	
WEIGHT	0.045g
CUSTOMER DRAWING	
SCALE	NTS
SHEET	1 of 1
REV	F