

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION FEB , 2017.
 © COPYRIGHT 2017 By TE Connectivity ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	NEW DRAWING FORMAT	16FEB2016	GK	DB
	F	LINER CHANGE	07SEP2018	GK	DB

LABEL AND LINER DESIGN

Dimensions and specifications for the label and liner design:

- Overall width: 87.3 [3.436]
- Label width: 25.4 [1.000]
- Label height: 36.5 [1.437]
- Label spacing (top): 12.7 [.500]
- Label spacing (bottom): 2.9 [.112]
- Label spacing (left): 3.0 [.118]
- Label spacing (right): 27.9 [1.100]
- Label spacing (between rows): 42.2 [1.661]
- Label spacing (between columns): 9.1 [.360]
- Label spacing (between columns): 10 [.393]
- Label spacing (between columns): 29.1 [1.145]
- Label spacing (between columns): 2.5 [.100]
- Label spacing (between columns): R0.8 [R.030]
- Label spacing (between columns): R1.5 [R.060]
- Label spacing (between columns): 1.6 [.062]
- Label spacing (between columns): 2.9 [.112]

Material specifications:

- HIGH OPACITY WHITE COLOR
- CLEAR (COLORLESS)
- AUTO ALIGN HOLES IN LINER

PRESENTATION

Dimensions and specifications for the presentation drawing:

- Roll diameter: $\phi 90 \pm 10$ [3.543 ± .393]
- Label diameter: $\phi 25.4$ [1.000]

**OUTSIDE WOUND
 LABEL ACROSS: 3
 PER ROLL QTY: 2,500**

All dimensions in mm [Inch]

TE PN: CN2899-000

MATERIAL	CLEAR VINYL
ADHESIVE TYPE	ACRYLIC PERMANENT
LINEAR	WHITE KRAFT

TOLERANCES mm [INCH]		DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		MATERIAL		FINISH		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		CHK		APVD		NAME		TE Connectivity																						
LABEL HEIGHT:	±0.3 [.012]	LABEL WIDTH:	±0.3 [.012]	WEB WIDTH:	±0.8 [.031]	VERTICAL REPEAT:	±0.8 [.031]*	HORIZONTAL REPEAT:	±0.8 [.031]*	PRINT POSITIONING:	±0.8 [.031]*	LEFT MARGIN:	±0.4 [.016]	QUANTITY:	-0 % +2 %	*NON ACCUMULATING	0 PLC	±	1 PLC	±	2 PLC	±	3 PLC	±	4 PLC	±	ANGLES	±	FINISH	GLOSSY	THIS DRAWING IS A CONTROLLED DOCUMENT.	DWN	16FEB2017	CHK	GOPALAKRISHNA HV	16FEB2017	APVD	D.BURGAT	16FEB2017	NAME	D.BURGAT	TE Connectivity
LABEL HEIGHT:	±0.3 [.012]	LABEL WIDTH:	±0.3 [.012]	WEB WIDTH:	±0.8 [.031]	VERTICAL REPEAT:	±0.8 [.031]*	HORIZONTAL REPEAT:	±0.8 [.031]*	PRINT POSITIONING:	±0.8 [.031]*	LEFT MARGIN:	±0.4 [.016]	QUANTITY:	-0 % +2 %	*NON ACCUMULATING	0 PLC	±	1 PLC	±	2 PLC	±	3 PLC	±	4 PLC	±	ANGLES	±	FINISH	GLOSSY	THIS DRAWING IS A CONTROLLED DOCUMENT.	DWN	16FEB2017	CHK	GOPALAKRISHNA HV	16FEB2017	APVD	D.BURGAT	16FEB2017	NAME	D.BURGAT	TE Connectivity
MATERIAL		SEE TABLE		FINISH		GLOSSY		WEIGHT		0.129 g		SIZE		A2		CAGE CODE		00779		DRAWING NO		SBP100143WE2.5-T200		RESTRICTED TO		-		CUSTOMER DRAWING		SCALE		NTS		SHEET		1 of 1		REV		F		

UL-MARKING AND LABELLING SYSTEMS

PGIS2 - Marking and Labeling Systems, Limited Use - Component (UL 969)

File: MH61871 Product design: **SBP** Ribbon: TMS-XXX-RIBBON-4RPSCE

1471-9 (1/15)

CN2899-000