



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - TE Connectivity Ltd. ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
F		NEW DRAWING	25OCT2018	GK	DB

LABEL AND LINER DESIGN

PRESENTATION



**OUTSIDE WOUND
 LABEL ACROSS: 3
 PER ROLL QTY: 5000**

All dimensions in mm [Inch]

TE PN: CR1509-000

UL-MARKING AND LABELLING SYSTEMS		
PGIS2 - Marking and Labeling Systems, Limited Use - Component (UL 969)		
File: MH61871	Product design: SBP	Ribbon: TMS-XXX-RIBBON-4RPSCE

TOLERANCES mm [INCH]
LABEL HEIGHT: ±0.3 [0.012]
LABEL WIDTH: ±0.3 [0.012]
WEB WIDTH: ±0.8 [0.031]
VERTICAL REPEAT: ±0.8 [0.031]*
HORIZONTAL REPEAT: ±0.8 [0.031]*
PRINT POSITIONING: ±0.8 [0.031]*
LEFT MARGIN: ±0.4 [0.016]
QUANTITY: -0 % +2 %
*NON ACCUMULATING

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±	1 PLC ±
2 PLC ±	3 PLC ±
4 PLC ±	ANGLES ±
MATERIAL: SEE TABLE	FINISH: GLOSSY

MATERIAL: CLEAR VINYL	ADHESIVE TYPE: ACRYLIC PERMANENT	LINEAR: WHITE KRAFT
DWN: GOPALAKRISHNA HV (25SEP2018)		CHK: D.BURGAT (25SEP2018)
APVD: D.BURGAT (25SEP2018)		NAME: SBP LABEL - RED
PRODUCT SPEC: TTDS-211		APPLICATION SPEC: 25.4 x 57.2mm [1.00 x 2.25inch]
WEIGHT: 0.202g	SIZE: A2	CAGE CODE: 00779
DRAWING NO: SBP100225RD5		RESTRICTED TO: -
CUSTOMER DRAWING		SCALE: NTS
SHEET: 1 of 1		REV: F