

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL	19SEP2017	YC	CW
	B1	ECR-23-181096	18JUL2023	BS	CW

NOTES:

1. TECHNICAL CHARACTERISTICS:
 INSULATION MATERIAL: PC
 RATED VOLTAGE: 830V
 RATED CURRENT: 40A
 INSULATION RESISTANCE: $\geq 400M\Omega$
 RATED IMPULSE VOLTAGE: 8KV
 POLLUTION DEGREE: 3
 FLAMMABILITY: UL94V-0
 MATING CYCLES: 500 CYCLES
 WIRE RANGE: 1.0~6.0mm² / 8AWG(10mm²)
 CAUTION, INSULATOR OF 8AWG(10mm²) CABLE $\leq \varnothing 6.1mm$.
 BREAK THE INSERT TO REMOVE 8AWG(10mm²) CONTACTS.

2. CONTACT TYPE: CRIMP CONTACT
 CONTACT NEED TO BE ORDERED SEPARATELY.
 (ORDER No. REFER TO DRAWING: T20400X10XX000)

注释:

1. 技术参数:
 绝缘材料: PC
 额定电压: 830V
 额定电流: 40A
 绝缘电阻: $\geq 400M\Omega$
 脉冲电压: 8KV
 污染等级: 3
 阻燃等级: UL94V-0
 插拔次数: 500次
 接线范围: 1.0~6.0mm² / 8AWG(10mm²)
 注意, 8AWG(10mm²) 线缆绝缘直径 $\leq \varnothing 6.1mm$.
 退出 8AWG(10mm²) 针时需要破坏零件.

接线类型: 冷压接

2. 端子需要单独订购.
 (订货号参考图面: T20400X10XX000)

T2111042101-007	HMN-004-M	HMN-004 MALE MODULE INSERT HMN-004 模块公插
PART NUMBER 料号	PART DESCRIPTION 描述	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC \pm
	1 PLC \pm
	2 PLC \pm
	3 PLC \pm
	4 PLC \pm
	ANGLES \pm
MATERIAL	FINISH
-	-
-	-

DWN	19SEP2017	 TE Connectivity	NAME	HMN-004-M	
CHK	19SEP2017				
APVD	19SEP2017				
PRODUCT SPEC	108-137060				
APPLICATION SPEC	114-137060	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
WEIGHT	-	A3	00779	©-T2111042101007	-
CUSTOMER DRAWING	SCALE	SHEET	OF	REV	
	3:2	1	1	B1	

1470-19 (3/13)