

DESCRIPTION

PRODUCT COVERED:

Component Connector, Cat. Nos. 207373-1, 207507-1, 208332-1.

GENERAL CHARACTER AND USE:

Cat Nos. 208332-1 and 207373-1 are straight type connectors intended to secure 1/2 in trade size extra flexible steel conduit and 1/2 in trade size flexible steel conduit respectively to 1/2 in trade size knockouts

* Cat. No. 207507-1 is a right angle connector intended to secure 1/2 in trade size flexible steel conduit to a 1/2 in trade size knockout.

ENGINEERING CONSIDERATIONS (NOT FOR UL REPRESENTATIVE USE):

Use - For use only in products where the acceptability of the combination is determined by Underwriters Laboratories Inc.

Conditions of Acceptability -

1. Cat. No. 208332-1 is for use with extra flexible steel conduit.
2. The connectors not been investigated as a grounding connector between the conduit and the enclosure.

***MARKING :**

All carton and product markings shall be legible. All markings on the product shall be permanent. The following types of markings or the equivalent are considered permanent; etched, molded, die stamped, paint stenciled, or indelibly stamped on a pressure sensitive label secured by adhesive and complying with the Standard for Marking and Labeling Systems, UL 969.

If there is not enough space on the carton or carton label, information marked on an information sheet packed in the smallest unit shipping carton is acceptable.

The following markings are required:

Marking	Location
Listees' name or trademark.	On product where readily visible after installation.
Cat. No.	On product where readily visible after installation or smallest unit shipping carton.
The temperature rating of Insulated Throat (@)	On product where readily visible after installation.

@ - This is optional marking. Temperature rating "125°C max or less