



P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	INITIAL RELEASE	13MAR2020	GK	MN

LABEL AND LINER DESIGN

PRESENTATION



All dimensions in mm [Inches]

TE PN: C73701-000


**OUTSIDE WOUND
LABEL ACROSS: 5
PER ROLL QTY: 25000**

MATERIAL	WHITE POLYESTER
ADHESIVE TYPE	PERMANENT
LINER	GLASSINE PAPER

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -
FINISH	-

MATERIAL
SEE TABLE

DWN	01SEP2006
CHK	13APR2020
APVD	13APR2020
PRODUCT SPEC	TTDS-073
APPLICATION SPEC	-
WEIGHT	0.007g

TE Connectivity			
NAME WP - WHITE POLYESTER LABELS			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	C2290	C-WP-095080-25-9	-
CUSTOMER DRAWING		SCALE	SHEET
		NTS	1 OF 1
		REV	C