



REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN APVD
B		ECR-20-003872	24FEB2020	GK MN

LABEL AND LINER DESIGN




PRESENTATION



All dimensions in mm [Inches]

TE PN: A07010-000

**OUTSIDE WOUND
LABEL ACROSS: 2
PER ROLL QTY: 2500**



TOLERANCES mm [INCH]
LABEL HEIGHT: ±0.3 [.012]
LABEL WIDTH: ±0.3 [.012]
WEB WIDTH: ±0.8 [.031]
VERTICAL REPEAT: ±0.8 [.031]*
HORIZONTAL REPEAT: ±0.8 [.031]*
PRINT POSITIONING: ±0.8 [.031]*
LEFT MARGIN: ±0.4 [.016]
QUANTITY: -0 % +2 %
*NON ACCUMULATING

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLG	±
1 PLG	±
2 PLG	±
3 PLG	±
4 PLG	±
ANGLES	±
FINISH	-

DWN GOPALAKRISHNA HV 05OCT2006	05OCT2006	NAME WP - WHITE POLYESTER LABELS
CHK K. MUNZ 05OCT2006	05OCT2006	TE Connectivity
APVD K. MUNZ	05OCT2006	SIZE A3
PRODUCT SPEC TTDS-073		CAGE CODE C2290
APPLICATION SPEC		DRAWING NO WP-381381-2.5-9
WEIGHT 0.131g		SCALE NTS
CUSTOMER DRAWING		SHEET 1 OF 1
		REV B

MATERIAL	WHITE POLYESTER
ADHESIVE TYPE	PERMANENT
LINER	GLASSINE PAPER