



P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	INITIAL RELEASE	26FEB2020	GK	MN

LABEL AND LINER DESIGN



PRESENTATION



All dimensions in mm [Inches]

TE PN: C17288-000

**OUTSIDE WOUND
LABEL ACROSS: 1
PER ROLL QTY: 1000**

MATERIAL	WHITE POLYESTER
ADHESIVE TYPE	PERMANENT
LINER	GLASSINE PAPER

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
ANGLES ± -	± -
MATERIAL SEE TABLE	FINISH -

DWN	23FEB2020
CHK	GOPALAKRISHNA HV
APVD	13MAR2020
PRODUCT SPEC	M.NUTTALL
APPLICATION SPEC	M.NUTTALL
WEIGHT	TTDS-073
	0.871g

TE Connectivity		NAME		WP - WHITE POLYESTER LABELS	
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
A3	C2290	C-WP-762127-1-9	-		
CUSTOMER DRAWING		SCALE	SHEET	REV	
		NTS	1 OF 1	D	