






REVISIONS					
REV	DATE	DESCRIPTION	BY	CHK	APPV
D8	06DEC2022	REVISED PER ECR-22-154840	RK	MT	



(MOUNTING DIMENSIONS FOR P.C.BORD,
TOLERANCE±0.1)
プリント基板取付寸法図
一般公差: ±0.1
(公差は累積しないこと)
(NON ACCUMULATE TOLERANCE)

- NOTES**
- △ MUST BE KEPT BETWEEN [X] AND 2
 - 2 THE MATING PLUG HSG.PART NUMBER; 174516, 174515, 174514, 917992, 917989, 917981
 - 3 RECOMMENDED MOUNTING SCREW; 3mm DIA, 6mm LENGTH (MAX.) PAN HEAD, CLASS 2 TAPPING SCREW SPECIFIED IN JIS B1115, B1122 (TIGHTENING TORQUE; 0.4N.m(4Kg-cm) MAX.)
 - 4 APPLICABLE PRODUCT SPEC NO. 108-5280, 108-5342
 - △ CIRCUI NUMBER; SEE FIG.1
POWER CIRCUIT NO. ① ~ ⑩
SIGNAL CIRCUIT NO. ⑪ ~ ⑤④
 - △ MARKING FOR DISCERNMENT OF THE CONTACT FINISH



REV	DESCRIPTION	PRE-TIN	SELECTIVE GOLD	CIRCUIT NO.	CONTACT	FINISH	HOUSING COLOR	P/N
OBSOLETE	59	PRE-TIN x 5L	SELECTIVE TIN (MATTE) SELECTIVE GOLD x 10	⑭ - ⑰	⑦ - ⑩	GRAY 灰色	9-5178764-6	
OBSOLETE	55	PRE-TIN x 40	SELECTIVE TIN (MATTE) SELECTIVE GOLD x 22	---	① - ④, ⑥ - ⑨	YELLOW 黄色	5-5178764-7	
OBSOLETE	54	PRE-TIN x 42	SELECTIVE TIN (MATTE) SELECTIVE GOLD x 24	---	② - ⑤, ⑦ - ⑩, ⑫ - ⑮	YELLOW 黄色	4-5178764-7	
OBSOLETE	53	PRE-TIN x 12	SELECTIVE TIN (MATTE) SELECTIVE GOLD x 52	⑦ - ⑩	① - ④	GRAY 灰色	3-5178764-6	
OBSOLETE	52	PRE-TIN x 16	SELECTIVE TIN (MATTE) SELECTIVE GOLD x 48	---	① - ④	GRAY 灰色	2-5178764-6	
OBSOLETE	52	PRE-TIN x 16	SELECTIVE TIN (MATTE) SELECTIVE GOLD x 48	---	① - ④	NATURAL 自然色	2-5178764-1	
OBSOLETE	51	PRE-TIN x 16	SELECTIVE TIN (MATTE) SELECTIVE GOLD x 64	① - ⑰	① - ④	GRAY 灰色	1-5178764-6	
OBSOLETE	8	PRE-TIN x 52	TIN-LEAD SELECTIVE GOLD x 12	---	① - ④, ⑥ - ⑨, ⑫ - ⑮	YELLOW 黄色	8-178764-7	
OBSOLETE	7	PRE-TIN x 48	TIN-LEAD SELECTIVE GOLD x 16	---	③ - ⑥, ⑧ - ⑪	YELLOW 黄色	7-178764-7	
OBSOLETE	6	PRE-TIN x 55	TIN-LEAD SELECTIVE GOLD x 9	⑬ - ⑰	⑦ - ⑩	NATURAL 自然色	6-178764-1	
OBSOLETE	5	PRE-TIN x 40	TIN-LEAD SELECTIVE GOLD x 24	---	① - ④, ⑥ - ⑨, ⑫ - ⑮	YELLOW 黄色	5-178764-7	
OBSOLETE	4	PRE-TIN x 42	TIN-LEAD SELECTIVE GOLD x 22	---	② - ⑤, ⑦ - ⑩, ⑫ - ⑮	YELLOW 黄色	4-178764-7	
OBSOLETE	3	PRE-TIN x 12	TIN-LEAD SELECTIVE GOLD x 52	⑦ - ⑩	① - ④	YELLOW 黄色	3-178764-7	
OBSOLETE	3	PRE-TIN x 12	TIN-LEAD SELECTIVE GOLD x 52	⑦ - ⑩	① - ④	GRAY 灰色	3-178764-6	
OBSOLETE	2	PRE-TIN x 16	TIN-LEAD SELECTIVE GOLD x 48	---	① - ④	YELLOW 黄色	2-178764-7	
OBSOLETE	2	PRE-TIN x 16	TIN-LEAD SELECTIVE GOLD x 48	---	① - ④	GRAY 灰色	2-178764-6	
OBSOLETE	2	PRE-TIN x 16	TIN-LEAD SELECTIVE GOLD x 48	---	① - ④	NATURAL 自然色	2-178764-1	
OBSOLETE	1	PRE-TIN x 64	TIN-LEAD SELECTIVE GOLD x 64	① - ⑰	① - ④	YELLOW 黄色	1-178764-7	
OBSOLETE	1	PRE-TIN x 64	TIN-LEAD SELECTIVE GOLD x 64	① - ⑰	① - ④	GRAY 灰色	1-178764-6	
OBSOLETE	0	PRE-TIN x 64	PRE-TIN x 64	---	---	YELLOW 黄色	178764-7	
OBSOLETE	0	PRE-TIN x 64	PRE-TIN x 64	---	---	NATURAL 自然色	178764-2	
OBSOLETE	0	PRE-TIN x 64	PRE-TIN x 64	---	---	NATURAL 自然色	178764-1	




FIG.1

- 注記**
- △ [X] 面から2mmの範囲で測定
 - 2. 嵌合相手ハウジング型 174516, 174515, 174514, 917992, 917989, 917981
 - 3. 推奨取付ねじ; JIS B1115, B1122 タッピンねじ, なべ2種
呼び径3, 長さ6mm以下(締付トルク; 0.4N.m(4Kg-cm)以下)
 - 4. 適用製品規格番号; 108-5280, 108-5342
 - △ 回路番号; FIG.1参照のこと
パワー回路; ① ~ ⑩
シグナル回路; ⑪ ~ ⑤④
 - △ コンタクト仕上識別マーク

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIN T. SHINOHARA 03AUG05
CHK K. BETSUJI 03AUG05
NAME K. BETSUJI 03AUG05

PRODUCT SPEC
製品規格

APPLICATION SPEC
取付適用規格

SIZE A1 CAGE CODE 00779 DRAWING NO. 178764 RESTRICTED TO

WEIGHT 28.4 g

MATERIAL HOUSING : PBT CONTACT : BRASS

CUSTOMER DRAWING

SCALE 2:1 SHEET 1 of 1 REV D8