

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
J	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
		A		RELEASED	18 JUN 08	K.M	S.Y



Technical Specifications

- **Workable Cable Types** : Coaxial cables, Multi-core cables, Standard cables
- **Stripping Length** : 0.01 - 40.00 mm
- **Stripping Diameter** : 0.01 - 8.00 φ mm
- **Stripping Steps** : Max. 9
- **Cable Gripping** : Motor-driven, 10 phase programmable
- **Production Rate** : 600 /Hr (Varies with programming)
- **Processing Data Capacity** : 1000 cables processing data
- **PC Interface** : RS232C
- **Noise Level** : 50 dB
- **Power Supply** : AC 100 - 240 V
- **Dimensions** : 136 x 580 x 260 mm
- **Net Weight** : Approx. 10 kg

(Specifications subject to change without notice.)

Note: Recommended to conduct a sufficient pre-purchase test, as exceptions may apply to some cable types. Contact your local representative with your processing specifications.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. MARUYAMA 18 JUN 08	Tyco Electronics Corporation Kawasaki, Japan	
DIMENSIONS: 単位: 耗 mm		CHK H. TANAKA 18 JUN 08	NAME 名称	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD H. TANAKA 18 JUN 08	PRODUCT SPEC 製品規格	
0 PLC ± -		APPLICATION SPEC 取付適用規格		
1 PLC ± -		SIZE		
2 PLC ± -		CAGE CODE		
3 PLC ± -		DRAWING NO 番号		
4 PLC ± -		RESTRICTED TO		
ANGLES ± -		A3 00779 C-2047793-1		
MATERIAL 材料	FINISH 仕上	WEIGHT		SCALE 尺度
-	-	CUSTOMER DRAWING		SHEET 1 OF 1
				REV A