

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

REVISIONS

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

P	LTR	DESCRIPTION	DATE	DWN	APVD
B1		ADD NEW PART NUMBERS ECR-17-017601	30NOV2017	RI	EI
B2		REVISED PER ECR-18-000417	11JAN2018	RI	EI
B3		REVISED PRE ECR-18-006941	07MAY2018	RI	EI
B4		ADD NEW PART NUMBERS ECR-18-017312	08FEB2019	RI	EI

ワイヤレンジマーク  
WIRE RANGE

シリーズマーク  
SERIES MARK

21.7REF

1REF

3REF

AB±0.4

AA±0.4

AD±0.4

AC±0.4

B-B  
SCALE 8:1

C-C  
SCALE 8:1

∅AE REF

2.9REF

3.9REF

2.5REF

2.8REF

AF±0.5

9.3REF

2.5REF

トレードマーク  
TRADE MARK

接圧表示  
PRESSURE ID

めっきコード  
PLATING ID

18.3	3.4	4.8	3.9	3.2	3.09	3.1-3.4	3L	AWG16-14 1.25-2.2mmSQ	-	2	GOLD 0.38um MIN.	2298107-5
18.3	2.6	4.2	4.0	3.2	3.09	2.2-2.8	2L	AWG16-14 1.25-2.2mmSQ	-	P	Pd-Ni 0.38um MIN. GOLD 0.05um MIN.	6-2298107-9
17.8	2.6	4.2	4.0	2.9	2.9	1.8-2.8	L	AWG20-16 0.5-1.42mmSQ	-	2	GOLD 0.38um MIN.	2298107-4
17.8	2.3	3.6	3.74	2.3	2.15	1.2-2.6	M	AWG24-20 0.2-0.5mmSQ	-	2	Pd-Ni 0.38um MIN. GOLD 0.05um MIN.	6-2298107-8
17.8	1.3	2.6	2.5	1.8	1.81	0.8-1.4	S	AWG28-24 0.08-0.2mmSQ	-	2	GOLD 0.38um MIN.	2298107-3
17.8	1.3	2.6	2.5	1.8	1.81	0.8-1.4	S	AWG28-24 0.08-0.2mmSQ	-	2	GOLD 0.38um MIN.	2298107-2
17.8	1.3	2.6	2.5	1.8	1.81	0.8-1.4	S	AWG28-24 0.08-0.2mmSQ	-	2	GOLD 0.38um MIN.	2298107-1
寸法AF DIM AF	寸法AE DIM AE	寸法AD DIM AD	寸法AC DIM AC	寸法AB DIM AB	寸法AA DIM AA	適用被覆径 INSUL. RANGE	ワイヤレンジマーク SIZE ID	適用電線範囲 WIRE RANGE	接圧表示 PRESSURE ID	めっきコード PLATING ID	接点部めっき CONTACT POINT PLATING	型番 PART NUMBER

I 材料: 銅合金  
めっき: 全面ニッケル下地および接点部に表記載のめっき

I MATERIAL: COPPER ALLOY  
PLATING: DESCRIBED IN THE TABLE  
OVER NICKEL PLATING

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
単位: 概  
mm

MATERIAL  
材料  
SEE NOTETOLERANCES UNLESS  
OTHERWISE SPECIFIED:  
一般公差 ±0.3  
0-PLC ±0.5  
1-PLC ±0.1  
2-PLC ±0.01  
3-PLC ±0.005  
4-PLC ±  
ANGLES ±3°FINISH  
仕上  
SEE TABLE

DWN 15APR2016

Y. OKADA

CHK 18APR2016

E. TAKEMASA

APVD 18APR2016

N. YAMASAKI

PRODUCT SPEC

製品規格

108-5349

APPLICATION SPEC

取付適用規格

114-78030

WEIGHT

-

CUSTOMER DRAWING

NAME

名称

RECEPTACLE CONTACT,

FMLB, DYNAMIC D3000 SERIES

SIZE

A3

CAGE CODE

00779

DRAWING NO

C=2298107

RESTRICTED TO

-

TE Connectivity

SCALE

尺度

4:1

SHEET

1

OF

1

REV

B4

1470-19 (3/13)