

FOR MORE INFORMATION

Technical Support

Internet: www.te.com/ADM
USA: +1 (800) 522-6752
Canada: +1 (905) 470-4425
Mexico: +52 (0) 55-1106-0814
C. America: +52 (0) 55-1106-0814
South America: +55 (0) 11-2103-6000
Germany: +49 (0) 6251-133-1999
Great Britain: +44 (0) 8706-080208
France: +33 (0) 1-3420-8686
Netherlands: +31 (0) 73-6246-999
China: +86 (0) 400-820-6015

Follow us on Twitter for all the latest product news
@TEConnectivity, and on Facebook, TEConnectivity.



Introducing Raychem MIL-DTL-24643 ZEROHAL PROFIBUS Cables

www.te.com/ADM

© 2012 Tyco Electronics Corporation. All Rights Reserved.

6-1773447-0 ADM/RRD 5M 01/2012

Raychem, ZEROHAL, TE Connectivity, and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies.

PROFIBUS is a trademark of Profibus International. Other products, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information herein, nothing herein constitutes any guarantee that such information is error-free, or any other representation, warranty or guarantee that the information is accurate, correct, reliable current. The TE entity issuing this publication reserves the right to make any adjustments to the information contained herein at any time without notice. All implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose are expressly disclaimed. The dimensions herein are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.



KEY FEATURES

MIL-DTL-24643/62 qualified

Waterblocked and non-waterblocked constructions

Meets water tightness requirements when tested with ASTM D1411 synthetic sea water solution

Suitable for transmission rates up to 12 Mb/s

Compatible with commercially available PROFIBUS connectors

DESCRIPTION

MIL-DTL-24643 has been the governing specification for low smoke, zero halogen insulated and jacketed shipboard cables used by the United States Navy and other military marine applications.

TE Connectivity's Raychem-brand ZEROHAL cables meeting the PROFIBUS standard, as described in MIL-DTL-24643/62, are qualified to meet the rigorous requirements to flame, smoke emissions, halogen content and severe water-blocking requirements.

APPLICATIONS

Cables are used in communications, machinery control monitoring and instrumentation for:

- Military vessels - MIL-DTL-24643/62
- Cruise ships
- Freighters
- Tankers
- Industrial Automation

ELECTRICAL

150 ohm impedance

Transmission rates up to 12 Mb/s

Attenuation (dB/100 m maximum)

2 MHz:	1.0 dB
4 MHz:	2.5 dB
16 MHz:	5.0 dB
100 MHz:	13.5 dB
300 MHz:	24.0 dB

MATERIALS

Foamed polyethylene components

Low smoke, ZEROHAL jacket

STANDARDS & SPECS

Raychem Specification 1200

Raychem Specification 345

MIL-DTL-26463/62

PRODUCT OFFERING

Military Part Number	Type	TE Part No.	Description
M24643/62-01	LSPB2SD-1	5022M1809	22 AWG, bare copper, non-water blocked, shield and jacket
M24643/62-02	LSPB2SDW-1	5022W1809	22 AWG, bare copper, water blocked, shield and jacket
M24643/62-03	LSPB2SDOS-1	5022M5809	22 AWG, bare copper, non-water blocked, two shields and two jackets
M24643/62-04	LSPB2SDOSW-1	5022W0809	22 AWG, bare copper, water blocked, two shields and two jackets



CABLE CONSTRUCTION

5022M1809



5022M5809



5022W0809



5022W1809

