




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
D1		REVISED PER ECN-23-225110	08AUG2023	RK	MF



- ① HSG: LCP, COLOR - BLACK
- ② POSTS: PHOSPHOR BRONZE
- ③ FINISH: 0.00254-0.00508[.000100-.000200] TIN-LEAD OVER 0.00127[.000050] MIN NICKEL ON ENTIRE POST
- ④ THE NOTED DIMENSION APPLIES AT THE INTERSECTION OF THE POST AND HOUSING
- ⑤ RETENTION FEATURE FOR 1.57[.062] THICK PC BOARD PER MANUFACTURER'S DESIGN AND CUSTOMER'S APPROVAL. (SEE TABLE FOR LOCATIONS)

	1, 6	2	14.83 [.584]	4	5	6	104836-3
OBSOLETE	1,3,5,7,13,15,17,18	2,4,6,8,10,12,14,16	45.31 [1.784]	17	10	18	104836-2
OBSOLETE	NONE	2,4,5,7,9	24.99 [.984]	9	5	10	104836-1
	RETENTION FEATURE LOCATION	POST NUMBER OMITTED	B	A	NO OF ACTIVE POSN	NO OF POSN	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. SHUEY 2-24-92				
DIMENSIONS: INCHES		CHK R. FEIDI 2-28-92				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. FEIDI 2-28-92	NAME			
0 PLC ± -		PRODUCT SPEC	HDR ASSY,MOD II, RTANG, .100			
1 PLC ± -		APPLICATION SPEC	q			
2 PLC ± 0.13[.005]			SIZE A2	CAGE CODE 00779	DRAWING NO C=104836	RESTRICTED TO -
3 PLC ± -			SCALE 4:1 SHEET 1 OF 1 REV D1			
4 PLC ± -			CUSTOMER DRAWING			
ANGLES ± -						
FINISH ③						
HOUSING: ①						
POST: ②						