



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
01 ₀	RELEASED	6/3/98	6/3/1998

DESIGNED FOR USE WITH 0.085 SR CABLE	
CABLE ENTRY DIAMETER MINIMUM	
HOUSING	.089
CONTACT	.0204

COMPONENT	MATERIAL	FINISH
HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303	GOLD PLATE PER MIL-G-45204
DIELECTRIC	PTFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204
EMI GASKET	CONDUCTIVE ELASTOMER PER MIL-G-83528	N/A

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES

FRAC. ± 1/64 DEC. ± .005 ANGLES ± 1°

DRAWN BY *[Signature]* DATE 9/4/97

CHECKED BY *[Signature]*

APPD BY *[Signature]* 6/3/1998

M/A-COM
a Division of AMP Incorporated
140 Fourth Avenue
Waltham, MA 02154-7577

NOTES:
1. CAPTURED CENTER CONTACT

.XXX = in
XX.X = mm (REF)

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF M/A COM INTERCONNECT DIV. AND SHALL NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEM(S) WITHOUT WRITTEN PERMISSION.	USE ASSY PROCEDURE		TITLE FIELD REPLACEABLE 2-HOLE FLANGE MOUNT JACK RECEPTACLE DIRECT SOLDER ATTACHMENT	
	408-04880 NO. A.P. (90-025)		SIZE B	CODE IDENT NO. 26805
			9024-5014-00	REV 01 ₀
SCALE 5:1			SHEET 1 OF 1	

CUSTOMER DRAWING

AMP PART # 122255-1
SHEET 1 OF 1 REV A