




| REVISIONS | | | | |
|-----------|-----|---------------------------|-----------|----------|
| P | LTN | DESCRIPTION | DATE | OWN APVD |
| B2 | | REVISED PER ECO-15-004915 | 08APR2015 | AP DD |
| B3 | | REVISED PER ECN-24-252171 | 08MAR2024 | AP RS |




- ⚠ MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- ⚠ FINISH:
30μ" SELECTIVE GOLD IN CONTACT AREA. SELECTIVE TIN ON PCB TAILS, NICKEL OVERALL.
- 3. CONNECTORS SUPPLIED WITH MOUNTING SCREWS.




SCALE 4:1

REFER TO WWW.TE.COM FOR PRODUCT AVAILABILITY



RECOMMENDED PCB LAYOUT
 MIN BOARD THICKNESS 1.0



OFFSET BETWEEN BOARD AND BACKPLANE HOLE COLUMNS

RECOMMENDED PCB LAYOUT
 MIN BOARD THICKNESS 1.0

| KEY POSITION CHART | |
|--------------------|------|
| | NONE |
| | A |
| | B |
| | C |
| | D |
| | E |
| | F |
| | G |
| | H |

| | | | |
|----------|--------------|--------|-------------|
| OBSOLETE | H | ⚠ | 8-2110104-1 |
| | G | ⚠ | 7-2110104-1 |
| | F | ⚠ | 6-2110104-1 |
| | E | ⚠ | 5-2110104-1 |
| OBSOLETE | D | ⚠ | 4-2110104-1 |
| | C | ⚠ | 3-2110104-1 |
| | B | ⚠ | 2-2110104-1 |
| | A | ⚠ | 1-2110104-1 |
| | NONE | ⚠ | 2110104-1 |
| | KEY POSITION | FINISH | PART NUMBER |

THIS DRAWING IS A CONTROLLED DOCUMENT. DWG: Z. MILLER 20SEP2010
 CHK: D. DIXON 20SEP2010
 APVD: D. DIXON 20SEP2010

TE Connectivity

NAME: IMPACT, 5 PAIR, DAUGHTERCARD 10 COLUMN, LEFT GUIDED, SIGNAL MODULE, 0.39 EYELET

SIZE: A1 CAGE CODE: 2110104 DRAWING NO: 00779

RESTRICTED TO: CUSTOMER DRAWING

SCALE: 6:1 SHEET: 1 OF 1 REV: B3