

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	A	REVISED PER ECR-15-008877	17JUN2015	RS JL
-	-	B	REVISED PER ECR-15-011756	12AUG2015	RS JL
-	-	BI	REVISED PER ECR-18-006945	29MAY2018	NG MZ

NOTES:

1 MATERIAL:
 HOUSING: GF PBT, COLOR: BLACK
 CONTACTS: COPPER ALLOY, FINISH: Sn OVER Ni.

2 IP CODE

3 TE LOGO

4 N CODE

5 L CODE

6 PE CODE

7 RATED VOLTAGE

8 AREA FOR AGENCY APPROVAL LOGO

Technical drawings of a T-splitter connector. The drawings include:

- Front View (Left):** Shows the circular connector face with three ports. Dimensions include a diameter of $\phi 13.3$ and a height of 24.0. Callouts 4, 5, and 6 are present.
- Side View (Middle):** Shows the profile of the connector with a total length of 61.1. Callouts 3, 5, and 7 are present.
- Rear View (Right):** Shows the back of the connector with a diameter of $\phi 21.0$ (2X) and a height of 44.7. Callouts 2, 3, 6, 7, and 8 are present.
- Another Side View (Far Right):** Shows the connector from a different angle with a length of 16.3. Callouts 4 and 6 are present.

Dimensions and callouts are as follows:

- Front View: $\phi 13.3$, 24.0, $\phi 13.1$, 4, 5, 6
- Side View: 61.1, 5, 3, 7, 5
- Rear View: 16.3, $\phi 21.0$ 2X, 44.7, 2, 3, 6, 7, 8
- Another Side View: 16.3, 4, 6

3D VIEWS, FOR REFERENCE ONLY

3D perspective views of the T-splitter connector, showing the front and side profiles.

SCALE 1:1

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN		CHK		APVD		NAME	
mm		0 PLC	±	C. DAILY	24FEB2014	MOSTOLLER	24FEB2014			TE Connectivity	
		1 PLC	±0.3	PRODUCT SPEC		108-133014		SIZE		CAGE CODE	
		2 PLC	±0.20	APPLICATION SPEC		114-32111		DRAWING NO		RESTRICTED TO	
		3 PLC	±	WEIGHT		-		A2		-	
		4 PLC	±	SCALE		5:2		SHEET		OF	
		ANGLES	±3°	Customer Drawing		-		1		2	
		FINISH		-		-		REV		BI	

1471-9 (3/11)

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
-	-	SEE SHEET 1	-	-	-		

POLARIZATION KEYS

TYPE "A"	TYPE "B"	TYPE "C"
P/N 2213434-1	P/N 2213434-2	P/N 2213434-3

OBSOLETE		T-SPLITTER CONNECTOR SEALED VERS. NECTOR M, 3 POSITION	C	2213434-3
		T-SPLITTER CONNECTOR SEALED VERS. NECTOR M, 3 POSITION	B	2213434-2
		T-SPLITTER CONNECTOR SEALED VERS. NECTOR M, 3 POSITION	A	2213434-1
NOTE		DESCRIPTION	POL. KEYS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. DAILY 24FEB2014	TE Connectivity	
		CHK M. STOLLER 24FEB2014		
DIMENSIONS:		APVD	NAME	
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	T-SPLITTER, NECTOR M, 3 POSN, SEALED	
	0 PLC ± 1 PLC ±0.3 2 PLC ±0.20 3 PLC ± 4 PLC ±	APPLICATION SPEC	SIZE	CAGE CODE
MATERIAL	ANGLES ±3° FINISH	114-32111	A2	-
		WEIGHT	DRAWING NO	RESTRICTED TO
		Customer Drawing	G-2213434	-
			SCALE 2:1	SHEET 2 OF 2
				REV B1