


REVISIONS		
REV	DESCRIPTION	DATE
F	REVISED PER DCR R060148	03/22/2006



1 TUBING VFP21 MARKED AS SHOWN IN WHITE CHARACTERS ON SURFACE INDICATED

2 TUBING VFP21 IS UL RECOGNIZED, IS RATED 125°C [257°F], 600 V AND MEETS VW-1 FLAME TEST.

3 TUBING VFP21 IS CSA CERTIFIED AND MEETS VW-1 FLAME TEST.

4 TUBING FP21 IS UNMARKED AND MEETS REQUIREMENTS OF AMS-DTL-23053/5-112-0

5. WEIGHT PER LINEAR FOOT/304.8 mm:  
32.7 g/.072 lbs.

6. MATERIAL: BLACK POLYOLEFIN

If this document is printed it becomes uncontrolled. Check for the latest revision

4	4	30.48 m [100 ft] MINIMUM	1-603332-2
		1.22 m [4 ft] MINIMUM	603332-5
1	2 3	30.48 m [100 ft] MINIMUM	603332-2
		1.22 m [4 ft] MINIMUM	603332-1
MARKING	NOTES	LENGTH L	PART NUMBER

### SPECIFICATION CONTROL DRAWING

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN mm. INCH DIMENSIONS ARE IN BRACKETS. DECIMALS .XX ± .01 [0.004 in] .X ± .1 [0.04 in] ANGLES .X ± 0.5 DEG	DRAWN	UNGUYEN	03/22/2006	Tyco Electronics Corporation 300 Constitution Drive Menlo Park, CA, USA 94025 
	APPROVED	JBROOKS	03/22/2006	
	CAD NAME	R060148		TITLE
THIRD ANGLE PROJECTION			SIZE	B
	CODE IDENT. NO.	06090	DWG. NO.	603332
DO NOT SCALE THIS DRAWING				SHEET 1 OF 1