

D

С


В

4



-LABEL TO TE

MARKING SPECIFICATION



SAFETY ORGANIZATIONS THIS FILTER WILL BE FORMALLY REC THE LISTED AGENCY. THEREFORE, AL LATEST REVISION OF THE FOLLOWING

UL APPROVED

CSA APPROVED

OPERATING SPECIFICATION LINE CURRENT/VOLTAGE: 7A, 520VAC LINE FREQUENCY: 50/60Hz

MAXIMUM LEAKAGE CURRENT: 5mA @

OPERATING AMBIENT TEMPERATURE R

IN AN AMBIENT, Ta, HIGHER THAN CURRENT, Io, IS AS FOLLOWS: I o I

RELIABILITY SPECIFICATIONS STORAGE TEMPERATURE: -40°C TO +8 HUMIDITY: 21 DAYS @ 40°C AND 959

TEST SPECIFICATIONS INDUCTANCE, NOMINAL: 5mH

CAPACITANCE @ 1kHz LINE TO GROUND, NOMINAL: 0.3µF LINE TO LINE, NOMINAL: 1µF


DISCHARGE RESISTOR L/G I.R. 680KΩ 1W L/L I.R. $3M\Omega$ 1 W L/N I.R. XXX N/G I.R. XXX IR (NO DISCHARGE RESISTOR) 20°C

RECOMMENDED RECEIVING INSPECITO LINE TO GROUND FOR 1 MINUTE: 285 LINE TO LINE FOR 1 MINUTE: 2236

FILTER APPROVAL


THE BEST WAY TO SELECT AND QUAL ENGINEERING TO TEST THE UNIT IN

THIS DRAWING IS A C	CONTROLLED DOCUMENT.	DWN 06APR2021 BAPAT SAHAS CHKUDLO DOLOGAPR2021	-
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHRIS BOLLE APVD 06APR2021	
mm			- FOW
	0 PLC ±- 1 PLC ±0.5 2 PLC ±0.40 3 PLC ±0.130 4 PLC ±0.0500	PRODUCT SPEC - APPLICATION SPEC	DIN 7KE
	ANGLES ±-	-	0,22
MATERIAL -	FINISH -	WEIGHT _	A 3 00
-	-	CUSTOMER DRAWING	



TYPICAL INSERTION LOSS COMMON MODE 50/50 Ω ; DIFFERENTIAL MODE 50/50 Ω

MHz	0.01	0.05	0.15	0.5	1	3	5	10	30
СМ	54	56	48	71	82	70	65	40	16
DM	30	32	40	69	54	50	48	34	25



|470-|9 (3/|3)

REVISIONS DESCRIPTION DA ASE 06ARP		dwn BS	apvd C B	D
				U
COGNIZED, CERTIFIED OR APPRO ALL TEST/REQURIEMENTS SPECIFI IG AGENCY STANDARDS WILL BE N	IED I	BY N TI	ΗE	
7A 520V 50Hz/60Hz 40°C 7A 520V 50Hz/60Hz 40°C				
AC 230VAC, 50Hz RANGE @ RATED CURRENT: -25°C 40°C, THE MAXIMUM OPERATING $Ir - \sqrt{\frac{85 - T\alpha}{45}}$ 85°C % RH	TO +4	40°C		С
, 50% RH AND 100VDC, MIN: 6M <u>ON HIPOT</u> 356VDC SVDC IFY A FILTER IS FOR YOUR YOUR EQUIPMENT.	Ω			В
TE Connect VER LINE FILTER FOR N 35 RAIL INSTALLATION MS10BBSDDM CAGE CODE DRAWING NO 0779 C=7-1609968-2 SCALE 1:2 SHEET		STRIC -	TED TO	A

