

D

С


В

_

А


4






TYPICAL INSERTION LOSS COMMON MODE 50/50 Ω ; DIFFERENTIAL MODE 50/50 Ω

	001		DE OO,	0012, 0			IODE OG	,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	
MH z	0.01	0.05	0.15	0.5	1	3	5	10	30
СМ	57	56	58	51	50	48	35	33	31
DM	49	50	65	82	86	70	65	66	37



3	2								
			REVISIONS]		
		P LTR	DESCRIPTION	DATE	DWN	APVD			
		A	INITIAL RELEASE	12APR2021	BS	СВ	-		
							- [
	THE LISTED	R WILL BE AGENCY.	<u>NS</u> E FORMALLY RECOGNIZED, CER THEREFORE, ALL TEST/REQUR THE FOLLOWING AGENCY STAN	IEMENTS SPECIFIED	ΙΝ	CTED TO -			
L3' LOAD SIDE	UL APPROVED)	36A 440V 50Hz	/60Hz 40°C					
○ [┷] ╇ [┷] ╋	CSA APPROVE	D	36A 440V 50Hz	/60Hz 40°C					
	<u>operating s</u> line curren line freque	IT/VOLTAC	GE: 36A, 440VAC			THE			
	MAXIMUM LEA	KAGE CUF	RRENT: 8.5mA @ 230VAC, 50H	Z					
\odot	OPERATING A	MBIENT	TEMPERATURE RANGE @ RATED	CURRENT: -25°C TO	+40°	C C C C C C C C C			
	IN AN AMBIE	INT, Ta,	HIGHER THAN 40°C, THE MAX	IMUM OPERATING					
	CURRENT,Io,	15 A5 F	Io=Ir $\sqrt{\frac{85-Ta}{45}}$						
	<u>reliability</u> storage tem humidity: 2	1 P E R A T U R E	•						
SS _ MODE 50/50Ω	TEST SPECIF		S 1 5 mll						
5 10 30	INDUCTANCE, CAPACITANCE		_: I.JMH						
35 33 31 65 66 37	LINE TO GRO)UND, NOM GROUND,	MINAL: 1.86μF NOMINAL: 2.2μF DMINAL: 10μF						
-LABEL TO TE MARKING SPECIFICATION	DISCHARGE F L/L I.R. 2M L/N I.R. 1M L/G I.R. 2M N/G I.R. 1M IR (NO DISC	4Ω 1 W 4Ω 1 W 4Ω 1 W 4Ω 1 W	ESISTOR) 20°C, 50% RH AND	100VDC, MIN: 6MΩ			B		
	LINE TO GRO LINE TO LIN	<u>RECOMMENDED RECEIVING INSPECITON HIPOT</u> LINE TO GROUND FOR 1 MINUTE: 2632VDC LINE TO LINE FOR 1 MINUTE: 1892VDC							
	FILTER APPR		R 1 MINUTE: 1093VDC						
	THE BEST WA	Y TO SEL	LECT AND QUALIFY A FILTER T THE UNIT IN YOUR EQUIPME						
THIS DRAWING IS A CONTROLL	LED DOCUMENT. DWN BAPA CHK	12AI AT SAHAS 12AI	PR2021	TE Connectivi	ŧγ				
OTHER	ERANCES UNLESS	IS BOLLE	PR2021 NAME	-	,		-		
0 PLC I PLC 2 PLC 2 PLC	±- ±0.5 ±0.40		DIN 35 RAIL IN 36KEPS10AFPWHM				4		
3 PLC 4 PLC ANGLES	±0.130 APPLICA ±0.0500	TION SPEC	SIZE CAGE CODE DRAWING NO		RESTRIC	CTED TO	1		
MATERIAL FINISH	- WEIGHT	-	A 3 0 0 7 7 9 C-9 - 1 6	609968-1	-	_			
				CALE 1.3 SHEET OF	- I - I - I				

470-19 (3/13)



REVISIONS				
DESCRIPTION	DATE	DWN	APVD	