

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	16DEC2014	HMR	CW
	B	ECR-15-013292	16SEP2015	DL	CW
	BI	ECR-16-009730	06JUL2016	BS	CW
	C	ECR-21-105750	02JUL2021	BS	CW

M3 SCREW
RECOMMENDED TIGHTENING
TORQUE 0.5Nm

NOTES:

- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PBT
RATED VOLTAGE: 50 V
RATED CURRENT: 10 A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 0.8 KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.14-2.5 mm² (26-14 AWG)
CONTACT TYPE: CRIMP CONTACT
- CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20200X20XX000)

注释:

- 技术参数:
绝缘材料: PBT
额定电压: 50V
额定电流: 10A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 0.8 KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: 0.14-2.5 mm² (26-14 AWG)
接线类型: 冷压接
- 端子需要单独订购.
(订货号参考图面: T20200X20XX000)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	16DEC2014	RAGHAVENDRA H M	
		CHK	16DEC2014	CHRIS WANG	
		APVD	16DEC2014	XU XIANG	
		PRODUCT SPEC	108-137042		
		APPLICATION SPEC	114-137042		
		WEIGHT	-		
		CUSTOMER DRAWING			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME HD-008-F	
0 PLC		±-		SIZE	
1 PLC		±-		CAGE CODE	
2 PLC		±-		DRAWING NO	
3 PLC		±-		RESTRICTED TO	
4 PLC		±-		SCALE	
ANGLES		±-		SHEET	
FINISH		-		OF	
-		-		REV	
-		-		C	

T2020082201-001	HD-008-F HD-008母插(不锈钢螺丝)
T2020082201-000	HD-008-F HD-008母插
PART NUMBER 料号	DESCRIPTION 描述

SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
A3		-		T2020082201000			
SCALE		SHEET		OF		REV	
2:1		1		1		C	

1470-19 (3/13)