






P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	30 JUL 2020	GY	CW
	A1	ECR-20-016041	7 FEB 2021	GY	CW
	B	ECR-21-103103	13 MAY 2021	GY	CW
	C	ECR-21-111798	07 OCT 2021	WQR	CW





NOTES:

- TECHNICAL CHARACTERISTICS:
 INSULATION MATERIAL: PC
 RATED VOLTAGE: 50V
 RATED CURRENT: 1A
 INSULATION RESISTANCE: $\geq 400M\Omega$
 RATED IMPULSE VOLTAGE: 0.8KV
 POLLUTION DEGREE: 3
 MATING CYCLES: 500
 OPERATION TEMPERATURE: $-40^{\circ}C \sim +70^{\circ}C$

注释:

- 技术参数:
 绝缘材料: PC
 额定电压: 50V
 额定电流: 1A
 绝缘电阻: $\geq 400M\Omega$
 脉冲电压: 0.8KV
 污染等级: 3
 插拔次数: 500
 工作温度: $-40^{\circ}C \sim +70^{\circ}C$



T2113000201-200	HMN-RJ45-F CAT6A	HMN-RJ45 FEMALE MODULE INSERT, CAT6A HMN-RJ45 母插, CAT6A
PART NUMBER 料号	PART DESCRIPTION 描述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GINO.YAO 30 JUL 2020														
		CHK CHRIS.WANG 30 JUL 2020														
		APVD CHRIS.WANG 30 JUL 2020	NAME HMN-RJ45-F CAT6A													
DIMENSIONS: mm		PRODUCT SPEC 108-137516	RESTRICTED TO													
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-137516	SIZE A3	CAGE CODE 00779												
<table border="0"> <tr> <td>0 PLC</td> <td>±-</td> </tr> <tr> <td>1 PLC</td> <td>±-</td> </tr> <tr> <td>2 PLC</td> <td>±-</td> </tr> <tr> <td>3 PLC</td> <td>±-</td> </tr> <tr> <td>4 PLC</td> <td>±-</td> </tr> <tr> <td>ANGLES</td> <td>±-</td> </tr> </table>		0 PLC	±-	1 PLC	±-	2 PLC	±-	3 PLC	±-	4 PLC	±-	ANGLES	±-	WEIGHT -	DRAWING NO T2113000201200	
0 PLC	±-															
1 PLC	±-															
2 PLC	±-															
3 PLC	±-															
4 PLC	±-															
ANGLES	±-															
MATERIAL -		SCALE 1:1		SHEET 1 OF 1												
		CUSTOMER DRAWING		REV C												