

TWIST SPLICE WIRE CONNECTORS

TE Connectivity's (TE) wire connectors answer the need for inexpensive, insulated electrical terminations. They can be used in almost every type of residential and commercial application where multiple wires need to be brought together for a reliable termination. TE wire connectors, which include Wire Grip, Wing Grip, Twist Grip, Ground Grip and Cap Grip connectors, are designed to meet industry standard color-coding specifications and terminate the corresponding range of wire sizes. The screw-on wire connectors contain a live-action square spring which draws wires deep into the spring for a safe, positive "grip" of the wires.



Applications

- Lighting installation
- Residential building wiring
- Building equipment

Electrical

- Rated up to 600 volt max for building wiring
- Up to 1000 volt max in lighting fixtures/luminaires and signs

Mechanical

- Operating Temperature: 105° C (221°F)
- Designed for copper-copper wires only

Specifications

- UL 486C
- CSA 22.2. NO. 188 Certified

Materials

- UL94V-2 flame-retardant thermoplastic

Key Benefits

- Terminate multiple wire gauges into single splice
- Tool-less twist grip termination
- Color-coded to industry standard for sizes 22-8 AWG

Family of Products



Wiregrip
Connectors



Winggrip



Twistgrip



Groundgrip



Capgrip

Product Selection Information

Series	Color	WIRE RANGE (AWG)	WIRE COMBINATION		Description	TE Part Number
			Min	Max		
Wire Grip	Gray	22 - 14	2 #22	1 #16 w/1 #18 w/1 #20	CPGI-WC-WG-GR	2299502-1
	Blue	22 - 14	2 #22	3 #16	CPGI-WC-WG-BL	2299501-1
	Orange	22 - 14	1 #18 w/1 #20	4 #16 w/1 #20	CPGI-WC-WG-OR	2299503-1
	Yellow	22 - 10	3 #20 Sol	2 #12 w/2 #14	CPGI-WC-WG-YW	2299505-1
	Red	22 - 10	3 #18	2 #10 Sol w/2 #12 Str	CPGI-WC-WG-RD	2299504-1
Ground Grip	Green	14 - 10	2 #14	5 #12	CPGI-WC-GG-GN	2299511-1
Twist Grip	Tan	22 - 8	3 #22 Sol	4 #12	CPGI-WC-TG-TN	2299510-1
	Gray	18 - 8	3 #14 w/1 #18	3 #10	CPGI-WC-TG-GR	2299509-1
Wing Grip	Yellow	18 - 10	2 #18	3 #12 Sol	CPGI-WC-WNG-YW	2299508-1
	Red	18 - 8	3 #16	5 #12 Sol	CPGI-WC-WNG-RD	2299507-1
	Blue	14 - 6	2 #10 w/1 #12	3 #8 w/1 #12	CPGI-WC-WNG-BL	2299506-1
Cap Grip	Yellow	22 - 10	4 #22	3 #12	CPGI-WC-CG-YW	2299513-1
	Red	22 - 6	3 #20	1 #8 w/3 #12 Str	CPGI-WC-CG-RD	2299512-1

te.com

© 2017 TE Connectivity Ltd. Family of Companies. All Rights Reserved. TE, TE Connectivity, and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies. Other logos, product and Company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

1-1773884-6 JN 03/2017

USA: +1 (800) 522-6752
 Canada: +1 (905) 475-6222
 Mexico: +52 (0) 55-1106-0800
 Latin/S. America: +54 (0) 11-4733-2200
 Germany: +49 (0) 6251-133-1999

UK: +44 (0) 800-267666
 France: +33 (0) 1-3420-8686
 The Netherlands: +31 (0) 73-6246-999
 China: +86 (0) 400-820-6015