

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT copyright.dBTe- ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
D		rep 15 0.8±0.15 WAS 0.8-+0.1	25OCT2018	PB	XR
E		TITLE BLOCK CORRECTED	04MAR2021	FB	XR
F		Drawing update	30JAN2023	NE	XR

LES LEVRES DOIVENT ETRE EXEMPTES DE BAVURE, COUPE OU DEFAUT D ASPECT...  
 NO BURR, CRACKS OR DEFAULT PERMITTED ON LIPS...

JOINT UNIFILAIRE / SINGLE WIRE SEAL  
 COUPE A-A / SECTION A-A

LES SURFACES INTERIEURES DOIVENT ETRE EXEMPTES DE DEFAUT, BAVURE, COUPURE OU DEFORMATION...  
 INSIDE AREAS MUSN'T PRESENT BURR, CRACK, DEFORMATION...

Notes:

-Bavure du point d'injection située dans une zone non fonctionnelle doit être inférieure à 0.4mm de hauteur et 0.3mm d'épaisseur.  
 -An injection point burr located in a no fonctional area must be less than 0.4mm high and 0.3mm thick  
 -Cotes fonctionnelle A-B-C/Functional dimensions A-B-C

CONDITIONEMENT / PACKAGING

-Sachets hermetiques dans carton suivant norme GALIA  
 -Sealed bags in box according to GALIA standard

BOUCHON / CAVITY PLUG  
 COUPE A-A / SECTION A-A

Echelle 3.000  
 Scale 3.000

DESIGNATION DESCRIPTION	COULEUR COLOR	REF PRONER PN PRONER	A	B	C	REF PSA PN PSA	REF RENAULT PN RENAULT	REF TE PN TE	MASSE WEIGHT
JOINT UNIFILAIRE A SERTIR SINGLE WIRE SEAL SECTION : 3 A (TO) 6 mm <sup>2</sup>	VERT / GREEN SIMILAR TO RAL6001	P8010489526	11.8	3	5.3	9637215880	8200 072 611	1544316-1	0.443 g
JOINT UNIFILAIRE A SERTIR SINGLE WIRE SEAL SECTION : 7 A (TO) 10 mm <sup>2</sup>	ORANGE / ORANGE SIMILAR TO RAL2003	P8010589526	11.8	4.5	6.8	9637215980	8200 072 613	1544316-2	0.447 g
BOUCHON D'ETANCHEITE SEALING PLUG	BLANC / WHITE SIMILAR TO RAL9010	P8010689526	11.8	1.5	6.8	9637216080	8200 402 054	1544316-3	0.622 g

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. CORONELLI 07NOV2007	TE Connectivity													
DIMENSIONS: mm		CHK P. CHARLES														
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. DAHER 07NOV2007	NAME													
<table border="1"> <tr><td>1. PLC</td><td>±</td></tr> <tr><td>2. PLC</td><td>±0.15</td></tr> <tr><td>3. PLC</td><td>±</td></tr> <tr><td>4. PLC</td><td>±</td></tr> <tr><td>ANGLES</td><td>±2°</td></tr> <tr><td>FINISH</td><td>-</td></tr> </table>		1. PLC	±	2. PLC	±0.15	3. PLC	±	4. PLC	±	ANGLES	±2°	FINISH	-	PRODUCT SPEC 108-15346	SINGLE WIRE SEAL AND PLUG	
1. PLC	±															
2. PLC	±0.15															
3. PLC	±															
4. PLC	±															
ANGLES	±2°															
FINISH	-															
MATERIAL SILICONE		APPLICATION SPEC 411-15697	SIZE A2	CAGE CODE 00779												
		WEIGHT VOIR TABLE	DRAWING NO C-1544316	RESTRICTED TO												
		CUSTOMER DRAWING	SCALE 8.000	SHEET OF REV F												

1471-9 (3/13)