

4

3

2

1

© - TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
D2	REVISED	ECR-23-185274	04SEP2023	AG	RK

パネル取付け寸法
MOUNTING DIMENSION FOR PANEL

- ① IN COUPLING WITH THE PLUG HOUSING MATING SATISFIES FUNCTION.
- 2. APPLIED CONTACT PN 170221, 170222
- 3. PRODUCT SPECIFICATION NUMBER: 108-5099
- ④ TO BE MEASURED WITHIN 2mm FROM -A-
- 5. IN COUPLING WITH THE PLUG HOUSING MATING FORCE 29.4N (3kg) MAX. WITHOUT RECEPTACLE CONTACT.
- ⑥ CENTERLINE OF CONTACT

- ① 相手ハウジングと所定の機能を満たして嵌合出来ること。
- 2. 使用コンタクト型番: 170221 及び 170222, その他
- 3. 製品規格番号: 108-5099
- ④ -A- 面より2mmの範囲で測定。
- 5. 相手ハウジングとの嵌合力は29.4N (3kg) 以下。但し、コンタクトは含まない。
- ⑥ コンタクトセンター迄の距離

OBSOLETE	YELLOW	171830-7
OBSOLETE	BLUE	171830-5
OBSOLETE	GREEN	171830-4
OBSOLETE	BROWN	171830-3
OBSOLETE	BLACK	171830-2
	NATURAL	171830-1
	COLOR	PART NUMBER

GENERAL TOLERANCE

10 ≥	: ±0.2
30 ≥ > 10	: ±0.25
100 ≥ > 30	: ±0.3
ANGLE	: ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	T.SHINOHARA	30JUL09
CHK	K.BETSUI	30JUL09
APVD	K.BETSUI	30JUL09
PRODUCT SPEC	SEE NOTE 3	
APPLICATION SPEC		
WEIGHT	0.000000	
CUSTOMER DRAWING		

MATERIAL: 66 NYLON (UL94V-2)

FINISH: -

TE Connectivity

MULTI-INTER LOCK CONNECTOR
21 POSITION CAP HOUSING WITH FLANGE

SIZE	A2	CAGE CODE	00779	DRAWING NO	C=171830	RESTRICTED TO	-
SCALE	2:1	SHEET	1 of 1	REV	D2		

1471-9 (1/15)

171830

A