

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

By TE CONNECTIVITY Japan G.K.

ALL RIGHTS RESERVED.

REVISIONS

変更

P	LTR	DESCRIPTION	DATE	DWN	APVD
A2	REVIS	ECR-09-006707	24MAR2009	S.K	A.O
B	REVIS		28MAY2012	H.U	N.Y
C	REVIS	ECR-17-001114	31JAN17	HH	HY
C1	REVIS	ECR-23-194019	XXDEC2023	KP	AO

1939556-3

1939556-4

1939556-5

Dimensions: 13.9±0.1, 20.25, 11.4±0.1, 1.1, 2X (Ø2), 2.25, 4.5

Dimension: 47.15

Labels: RESISTANCE LABEL, DATE CODE

Dimensions: 19.6, 9.6

Part No: 1939556-1

SCALE 1:1

1939556-6

1939556-7

1939556-8

1939556-9

0.5W/20kΩ	1939556-9
0.5W/2.2kΩ	1939556-8
0.125W / 619Ω	1939556-7
0.125W / 590Ω	1939556-6
2W / 150Ω	1939556-5
0.5W / 120Ω	1939556-4
0.125W / 301Ω	1939556-3
0.125W / 487Ω	1939556-1
RESISTANCE	PART No.

① MATERIAL: 15% GLASS FILLED THERMOPLASTIC
COLOR: BLACK

② MATERIAL: 15% GLASS FILLED THERMOPLASTIC
COLOR: RED

3. MATERIAL OF SEAL : SILICONE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 耗
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

一般公差 ±0.3
0-PLC ±
1-PLC ±
2-PLC ±
3-PLC ±
4-PLC ±
ANGLES ±3°

MATERIAL
材料

FINISH
仕上

DWN IISEP2006

S. KUBOTA

CHK IISEP2006

J. AKASAKA

APVD IISEP2006

D. MITSUGI

PRODUCT SPEC

製品規格

APPLICATION SPEC

取付適用規格

WEIGHT

10.6 g

CUSTOMER DRAWING

NAME

名称

TE Connectivity

CAP ASSY 2P

AMPSEAL16 WITH RESISTANCE

SIZE

A3

CAGE CODE

00779

DRAWING NO

C-1939556

RESTRICTED TO

-

SCALE

2:1

SHEET

1

OF

1

REV

C1

1470-19 (3/13)