


TWO CONDUCTOR CABLE, MODIFIED FLUOROPOLYMER INSULATED, SHIELDED AND JACKETED,  
 150°C, 600 VOLT, LIGHTWEIGHT.

The complete requirements for procuring the wire described herein shall consist of this document.



Part Description	Wire Size Code	Shield Size (mm)	Jacket Thickness (mm) Min.	Overall				NSN 6145-99-038-4024	Def Stan 61-12(Part 33) Supplement 001 Table 9	
				Diameter (mm)		Weight (kg/ km)			Max. OD (mm)	Max. Weight (kg/ km)
				Target	Max.	Target	Max.			
55D1120-26-*/*-*	001	0.10	0.13	2.24	2.34	9.07	9.98	4024	2.54	10.43
55D1120-24-*/*-*	002	0.10	0.13	2.44	2.54	10.97	11.95	4025	2.72	12.53
55D1122-22-*/*-*	004	0.10	0.13	2.78	2.88	14.51	15.60	4026	3.06	16.96
55D1122-20-*/*-*	006	0.10	0.13	3.25	3.35	21.02	22.40	4027	3.60	24.09
55D1122-18-*/*-*	010	0.10	0.13	3.79	3.94	28.49	30.91	4028	4.08	32.34
55D1122-16-*/*-*	012	0.10	0.13	4.07	4.22	35.27	37.43	4029	4.54	39.12
55D1122-14-*/*-*	020	0.10	0.13	4.76	4.96	47.34	51.79	4030	5.48	55.96
55D1122-12-*/*-*	030	0.10	0.13	5.68	5.88	71.95	75.78	4031	6.44	83.55

**COLOUR CODE:** The '\*' in the part number shall be replaced by a standard colour code designator in accordance with Mil Std 681.  
 e.g. 55D1222-24-2/6-9, cores red/blue, jacket white.  
 Unless otherwise specified by the purchaser, component colours to be red and blue.

**NOTE:** Nato Stock Numbers (NSN) apply to red/blue cores, white jacket only.

**PERFORMANCE REQUIREMENTS:** To be tested to and meet the requirements of the issue in effect of Def Stan 61-12(Part 33) and Supplement 001, Table 9.

**MARKING REQUIREMENT:** Every 400 ±100 mm.  
 Mark shall be, e.g. 55D112#-XX DSP33/001-1S-YYY-2SJ-\*/\*-GB-SS-V  
 Where: "#" = Conductor material either 0 or 2 (see above part description)  
 "XX" = AWG size from part description  
 "YYY" = Wire Size Code

**NOTE:** Colour Code Designator "\*/\*-\*" is **NOT** required for red/ blue - white cable.  
 and "V" = the Year Code in accordance with the table below

<b>Code:</b>	10	11	12	13	14	15	16
<b>Year:</b>	2010	2011	2012	2013	2014	2015	2016

This drawing does not cover Armament cables, refer to 55DA112X.

**APPROVAL:** Electronic sign off - no signatures will appear.

Tyco Electronics UK Ltd  
 Faraday Road  
 Dorcan  
 SWINDON  
 SN3 5HH  
 UK

Registration Number:  
 550926 London, England

This drawing and the information set forth herein are the property of Tyco Electronics UK Ltd, and are to be held in trust and confidence. Publication, duplication, disclosure or use for any purpose not expressly authorised in writing by Tyco Electronics UK Ltd is prohibited.

This specification sheet takes precedence over documents referenced herein. As Tyco Electronics UK Ltd. reserve the right to make changes in construction without notice please contact Tyco Electronics UK Ltd to ensure that this document is the latest issue

Tel: 0800 267666  
 Fax: 01793 572516

Website: [www.tycoelectronics.com](http://www.tycoelectronics.com)  
 Email: [picuk@tycoelectronics.com](mailto:picuk@tycoelectronics.com)