

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

REVISIONS

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	24 JAN 2024	C.Z	Z.Z

1. SUPPLIED FORM: LOOSE PIECE PACKED INTO CARTON

1-2443906-3	H+S CABLE FOR 95MM2	A	45°	20.4	ORANGE	PA6 GF18	
2-2443906-3		B	135°				
3-2443906-3		C	55°				
4-2443906-3		D	85°				
5-2443906-3		E	95°				
6-2443906-3		F	125°				
7-2443906-3		G	35°				
8-2443906-3		H	145°				
1-2443906-2	H+S CABLE FOR 70MM2	A	45°	17.4	ORANGE	PA6 GF18	
2-2443906-2		B	135°				
3-2443906-2		C	55°				
4-2443906-2		D	85°				
5-2443906-2		E	95°				
6-2443906-2		F	125°				
7-2443906-2		G	35°				
8-2443906-2		H	145°				
1-2443906-1	H+S CABLE FOR 50MM2	A	45°	15.3	ORANGE	PA6 GF18	
2-2443906-1		B	135°				
3-2443906-1		C	55°				
4-2443906-1		D	85°				
5-2443906-1		E	95°				
6-2443906-1		F	125°				
7-2443906-1		G	35°				
8-2443906-1		H	145°				
P/N	REV	FOR WIRE DIAMETER	CODE	A	B	COLOUR	MATERIAL

3D VIEW

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN CH,Zhai 24 JAN 2024

CHK J.Li 24 JAN 2024

APVD Z.Zhou 24 JAN 2024

PRODUCT SPEC 108-160914

APPLICATION SPEC 114-160559

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME IPT HD 1P COVER FOR 50/70/95MM2

SIZE A3 CAGE CODE 00779 DRAWING NO C-2443906 RESTRICTED TO -

SCALE 1:1 SHEET 1 OF 1 REV A

DIMENSIONS:
mm

MATERIAL
SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±0.5
2 PLC	±0.5
3 PLC	±0.5
4 PLC	±0.5
ANGLES	±
FINISH	-

1470-19 (3/13)