

4

3

2

1

THIS DRAWING IS UNPUBLISHED  
 RELEASED FOR PUBLICATION 2015  
 © COPYRIGHT 2015 BY - TE CONNECTIVITY ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
-	-	NC	NEW RELEASE PER E.O. P19459	12FEB2014	-	RDR
		A	REVISED PER E.O. P21009	19JUL2007	-	RDR
		A1	REVISED PER ECO-15-001798	19MAR2015	VNB	DM
		A2	REVISED PER PCN E-20-000705	27JAN2020	PK	DM

Ø 1.750 ± .010  
[44.45 ± .25]

MAIN POLARIZING KEY

0421-03-1806

1.030 [26.16]

.505 [12.83]

.100 [2.54]

(3.217) [81.70]

HD34-18-XXPSX-059

HD34-18-XXPSX-059 19M0517

CABLE CLAMP ASSEMBLY HIDDEN VIEW

4 DATE CODE: IDENTIFIES THE YEAR, MONTH, DAY AND HOUR OF ASSEMBLY.  
 YEAR: FIRST AND SECOND DIGITS. (14=2014)  
 MONTH: THIRD DIGIT, EXCLUDING 1. A=JAN., B=FEB., C=MARCH... (K=OCT.)  
 DAY: FOURTH AND FIFTH DIGITS (14=14th DAY)  
 HOUR: SIXTH AND SEVENTH DIGITS (11=11AM)

3 MATERIAL:  
 ADAPTER: 6061-T6 ALUMINIUM ALLOY,  
 GROMMET: SILICONE VMQ (RED),  
 RETAINER RING: PA66 GF10.

2. THE CONNECTOR MATES WITH HD36-24-XXP/SX-XXXX  
 X - SEAL DESIGNATION, XX = NUMBER OF CAVITIES,  
 XXXX = MODIFICATION DESIGNATION.

1. FOR ARRANGEMENT OF CONTACT LOCATION  
 SEE ENVELOPE DRAWING 0425-013-1800.

NOTES:

3 ADAPTER  
 4 CABLE CLAMP ASSEMBLY  
 1.500-18 UNEF REF.

3D VIEW

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. MALAGON 30 JAN 2007		
DIMENSIONS: INCHES [mm]		CHK B. BAYFORD 06 FEB 2007		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. REED 12 FEB 2007	NAME RECEPTACLE CONNECTOR SHELL SIZE 18 BAYONET COUPLING MOD -059 HD30 SERIES	
0 PLC ±-		PRODUCT SPEC 108-151014	SIZE A3	CAGE CODE -
1 PLC ±-		APPLICATION SPEC 114-151014	DRAWING NO C=HD34-18-XXP/SX-059	RESTRICTED TO -
2 PLC ±-		WEIGHT 109g	SCALE NONE	
3 PLC ±.010 [±.254]		Customer Drawing	SHEET 1	OF 1
4 PLC ±-			REV A2	
ANGLES ±° 30' 0"				
FINISH -				

1470-19 (3/11)