


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - LEB-0619P-4 ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	DRAWING FORMAT UPDATE	27DEC2018	GK	KM



**LABEL ACROSS: 5**  
**LABELS PER SHEET: 220**  
**LABELS PER PACK: 2200**  
**SHEETS PER PACK: 10**

**All dimensions in mm [INCHES]**

Print Colour	Description	Material	Nom. Thickness	Adhesive Type	Part number
	LEB-0636P-8A	PE200 Silver Polyester	0.05 mm	Acrylic, permanent	1-1768033-6
	LEB-0636P-9	PE201 White Polyester	0.05 mm	Acrylic, permanent	1-1768033-7
	LEB-0636P-8	PE202 Silver-grey Polyester	0.05 mm	Acrylic, permanent	1-1768033-5
	LEB-0636P-4	PE216 Yellow Polyester	0.05 mm	Acrylic, permanent	1-1768033-4
	LEB-0636PF-4	GW201 Yellow Polyester cloth	0.10 mm	Acrylic, permanent	1-1768033-8
	LEB-0636S-8A	SV100 Safety film silver	0.05 mm	Acrylic, permanent	1-1768033-9

TOLERANCES mm [INCHES] LABEL HEIGHT: ±0.3 [.012] LABEL WIDTH: ±0.3 [.012] WEB WIDTH: ±0.8 [.031] VERTICAL REPEAT: ±0.8 [.031] HORIZONTAL REPEAT: ±0.8 [.031] PRINT POSITIONING: ±0.8 [.031] LEFT MARGIN: ±0.4 [.016] QUANTITY: -0% +2% *NON ACCUMULATING		THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: mm [INCHES] 		DWN 27DEC2018 GOPALAKRISHNA HV CHK 27DEC2018 K. MUNZ APVD 27DEC2018 K. MUNZ PRODUCT SPEC APPLICATION SPEC WEIGHT 0.07g CUSTOMER DRAWING		TE Connectivity NAME LEB - POLYESTER LABELS ON SHEET SIZE A2 CAGE CODE C2290 DRAWING NO. C=LEB-0636 RESTRICTED TO SCALE NTS SHEET 1 of 1 REV B	
---	--	---	--	--	--	---	--