

TE P/N	TE CD	Nanonics P/N	Part Description
1589470-1	1589470	SSG009M5CN	Dualobe, 1 row, gold, 9 position, receptacle, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.0 x .200 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1589470-2	1589470	SSL015M5KN	Dualobe, 1 row, LCP, 15 position, receptacle, vertical mount, thru hole termination, .090 long tin/lead leadframe, 1.0 x .200 mounting screw w/ 4 standoffs, thread for 1.0 jackscrews.
1589470-3	1589470	SSL025M5CN	Dualobe, 1 row, LCP, 25 position, receptacle, vertical mount, thru hole termination, .090 long tin/lead leadframe, 1.0 x .200 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1589470-4	1589470	SSL037M5N	Dualobe, 1 row, LCP, 37 position, receptacle, vertical mount, thru hole termination, .090 long, tin/lead leadframe, thread for 1.0 jackscrews.
1589470-5	1589470	SSM009M5CN	Dualobe, 1 row, metal, 9 position, receptacle, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.0 x .200 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1589470-6	1589470	SSM009M5HN	Dualobe, 1 row, metal, 9 position, receptacle, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1589470-7	1589470	SSM009M5LQ	Dualobe, 1 row, metal, 9 position, receptacle, vertical mount thru hole termination, .090 long, tin/lead leadframe, 1.2 x .200 mounting screw w/ 2 standoffs, thread for 1.2 jackscrews.
1589470-8	1589470	SSM015M5CN	Dualobe, 1 row, metal, 15 position, receptacle, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.0 x .200 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1589470-9	1589470	SSM015M5LQ	Dualobe, 1 row, metal, 15 position, receptacle, vertical mount thru hole termination, .090 long, tin/lead leadframe, 1.2 x .200 mounting screw w/ 2 standoffs, thread for 1.2 jackscrews.
1-1589470-0	1589470	SSM025M5CN	Dualobe, 1 row, metal, 25 position, receptacle, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.0 x .200 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1-1589470-1	1589470	SSM025M5HN	Dualobe, 1 row, metal, 25 position, receptacle, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1-1589470-2	1589470	SSM025M5LQ	Dualobe, 1 row, metal, 25 position, receptacle, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.2 x .200 mounting screw w/ 2 standoffs, thread for 1.2 jackscrews.
1-1589470-3	1589470	SSM051M5CN	Dualobe, 1 row, metal, 51 position, receptacle, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.0 x .200 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1-1589470-4	1589470	SSM025M5N	Dualobe, 1 row, metal, 25 position, receptacle, vertical mount, thru hole termination, .090 long, tin/lead leadframe, thread for 1.0 jackscrews.
1-1589470-5	1589470	SSL009M5CN	Dualobe, 1 row, LCP, 9 position, receptacle, vertical mount, thru hole termination, .090 long tin/lead leadframe, 1.0 x .200 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1-1589470-6	1589470	SSM005M5CN	Dualobe, 1 row, metal, 5 position, receptacle, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.0 x .200 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1-1589470-7	1589470	SSM015M5KN	Dualobe, 1 row, metal, 15 position, receptacle, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.0 x .200 mounting screw w/ 4 standoffs, thread for 1.0 jackscrews.
1-1589470-8	1589470	SSM005M5AQ	Dualobe, 1 row, metal, 5 position, receptacle, vertical mount thru hole termination, .090 long, tin/lead leadframe, 1.2 x .160 mounting screws, thread for 1.2 jackscrews.
1-1589470-9	1589470	SSM005M5IQ	Dualobe, 1 row, metal, 5 position, receptacle, vertical mount thru hole termination, .090 long, tin/lead leadframe, 1.2 x .200 mounting screws, thread for 1.2 jackscrews.
2-1589470-0	1589470	SSM051M5HN	Dualobe, 1 row, metal, 51 position, receptacle, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.