

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → Solution Series

## General Information

<b>Extended Product Type:</b>	BO3
<b>Product ID:</b>	1SNA164406R2400
<b>EAN:</b>	3472591644067
<b>Catalog Description:</b>	BO3 Distribution Terminal Blocks Busbars
<b>Long Description:</b>	Copper bar for distribution These products offer the possibility to distribute potential on various types of blocks and in some case to connect ground wires of 2.5 mm <sup>2</sup> Application : Connection of protect.

## Ordering

<b>Minimum Order Quantity:</b>	1 piece
<b>Customs Tariff Number:</b>	85389099

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNC160001C0207-CH-G Distribution terminals
<b>Instructions and Manuals:</b>	1SNC160001C0207-CH-G Distribution terminals

## Dimensions

<b>Product Net Width:</b>	1000 mm
<b>Product Net Height:</b>	10 mm
<b>Product Net Depth / Length:</b>	3 mm
<b>Product Net Weight:</b>	0.281 kg

## Technical

<b>Function:</b>	Busbars
<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

<b>Suitable For:</b>	D1.5/6.NT.ADO
	D10/10.NT.L
	D16/12.NT.L
	D2.5/5.NT.L
	D2.5/5.NTLP.L
	D2.5/8.NT.ADO
	D35/16.NT.L
	D4/6.LNTP
	D4/6.LNTP.L
	D4/6.NT.L
	D4/6.NTLP
	D6/8.NT.L
	M10/10.NT
	M16/12.NT
	M35/16.NT
	M4/6.NT
	M6/8.NT
	MA2.5/5.NT

## Certificates and Declarations (Document Number)

<b>Declaration of Conformity - CE:</b>	1SND225030U1000
<b>EAC Certificate:</b>	1SND161009A1100
<b>Environmental Information:</b>	1SND220054E1001
<b>Instructions and Manuals:</b>	1SNC160001C0207-CH-G Distribution terminals

## Classifications

<b>Object Classification Code:</b>	X
<b>E-nummer:</b>	2925685
<b>ETIM 4:</b>	EC000485 - Neutral busbar
<b>ETIM 5:</b>	EC000485 - Neutral busbar
<b>ETIM 6:</b>	EC000485 - Neutral busbar

## Container Information

<b>Package Level 1 Units:</b>	1 piece
<b>Package Level 1 Gross Weight:</b>	0.28 kg
<b>Package Level 1 EAN:</b>	3472591644067
<b>Package Level 2 Units:</b>	200 piece
<b>Package Level 3 Units:</b>	36000 piece

