

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories  
→ Jumper Bars

## General Information

<b>Extended Product Type:</b>	BJM10
<b>Product ID:</b>	1SNA173614R2400
<b>EAN:</b>	3472591736144
<b>Catalog Description:</b>	BJM 10 5 POLES Jumper Bars
<b>Long Description:</b>	BJM10 - Jumper Bars - 5 poles - - 10mm Spacing.

## Ordering

<b>Minimum Order Quantity:</b>	10 piece
<b>Customs Tariff Number:</b>	85369010

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNC160001C0207-CH-J Accessories
<b>Instructions and Manuals:</b>	1SNC160001C0207-CH-J Accessories

## Dimensions

<b>Product Net Weight:</b>	13 g
----------------------------	------

## Technical

<b>Function:</b>	Jumper Bars
<b>Rated Current (I<sub>n</sub>):</b>	Main Circuit 57 A
<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

## Certificates and Declarations (Document Number)

<b>Instructions and Manuals:</b>	1SNC160001C0207-CH-J Accessories
<b>RoHS Information:</b>	1SND230492F0201

## Classifications

<b>Object Classification Code:</b>	X
<b>ETIM 4:</b>	EC000489 - Cross-connector for terminal block
<b>ETIM 5:</b>	EC000489 - Cross-connector for terminal block
<b>ETIM 6:</b>	EC000489 - Cross-connector for terminal block

## Container Information

<b>Package Level 1 Units:</b>	10 piece
-------------------------------	----------

<b>Package Level 1 Width:</b>	155 mm
<b>Package Level 1 Depth / Length:</b>	200 mm
<b>Package Level 1 Height:</b>	5 mm
<b>Package Level 1 Gross Weight:</b>	0.13 kg
<b>Package Level 1 EAN:</b>	3472591736144
<b>Package Level 2 Units:</b>	500 piece
<b>Package Level 2 Width:</b>	175 mm
<b>Package Level 2 Depth / Length:</b>	227 mm
<b>Package Level 2 Height:</b>	130 mm
<b>Product Packing Type:</b>	Bag

