

TE P/N	TE CD	Nanonics P/N	Part Description
1589602-1	1589602	STM00911816M6CN	Dualobe, 2 row, metal, 9 position, special 11816, receptacle, horizontal mount, 90 thru hole termination, .125 long, tin/lead leadframe, 1.0 x .200 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1589602-2	1589602	STM01511816M6AN	Dualobe, 2 row, metal, 15 position, special 11816, receptacle, horizontal mount, 90 thru hole termination, .125 long, tin/lead leadframe, 1.2 x .160 mounting screw, thread for 1.0 jackscrews.
1589602-3	1589602	STM02511816M6AN	Dualobe, 2 row, metal, 25 position, special 11816, receptacle, horizontal mount, 90 thru hole termination, .125 long, tin/lead leadframe, 1.2 x .160 mounting screw, thread for 1.0 jackscrews.
1589602-4	1589602	STM03711816M6CN	Dualobe, 2 row, metal, 37 position, special 11816, receptacle, horizontal mount, 90 thru hole termination, .125 long, tin/lead leadframe, 1.0 x .200 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1589602-5	1589602	STM06511816M6CN	Dualobe, 2 row, metal, 65 position, special 11816, receptacle, horizontal mount, 90 thru hole termination, .125 long, tin/lead leadframe, 1.0 x .200 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1589602-6	1589602	STM01511816M6HN	Dualobe, 2 row, metal, 15 position, special 11816, receptacle, horizontal mount, 90 thru hole termination, .125 long, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1589602-7	1589602	STM02511816M6HN	Dualobe, 2 row, metal, 25 position, special 11816, receptacle, horizontal mount, 90 thru hole termination, .125 long, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1589602-8	1589602	STM05111816M6HN	Dualobe, 2 row, metal, 51 position, special 11816, receptacle, horizontal mount, 90 thru hole termination, .125 long, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1589602-9	1589602	STM03711816M6HN	Dualobe, 2 row, metal, 37 position, special 11816, receptacle, horizontal mount, 90 thru hole termination, .125 long, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1-1589602-0	1589602	STM03711816M6SN	Dualobe, 2 row, metal, 37 position, special 11816, receptacle, horizontal mount, 90 thru hole termination, .125 long, tin/lead leadframe, 1.0 x .160 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1-1589602-1	1589602	STM037M61FN	Dualobe, 2 row, metal, 37 position, receptacle, horizontal mount, 90 thru hole termination, .125 long tin/lead leadframe, 1.0 x .250 mounting screw w/ 4 standoffs, thread for 1.0 jackscrews.
1-1589602-2	1589602	STM009M61FN	Dualobe, 2 row, metal, 9 position, receptacle, horizontal mount, 90 thru hole termination, .125 long tin/lead leadframe, 1.0 x .250 mounting screw w/ 4 standoffs, thread for 1.0 jackscrews.
5-1589680-0	1589602	STM00911309M6DQ	Dualobe, 2 row, metal, 9 position, special 11309, receptacle, horizontal mount, 90 thru hole termination, tin/lead leadframe, 1.2 x .160 mounting screw w/ 2 standoffs, thread for 1.2 jackscrews.
7-1589680-6	1589602	STM01511016M6S	Dualobe, 2 row, metal, 15 position, special 11016, receptacle, horizontal mount, 90 thru hole termination, .125 long, tin/lead leadframe, 1.0 x .160 mounting screw w/ 2 standoffs.
8-1589680-7	1589602	STM01511309M6DQ	Dualobe, 2 row, metal, 15 position, special 11309, receptacle, horizontal mount, 90 thru hole termination, tin/lead leadframe, 1.2 x .160 mounting screw w/ 2 standoffs, thread for 1.2 jackscrews.
3-1589681-3	1589602	STM02511309M6DQ	Dualobe, 2 row, metal, 25 position, special 11309, receptacle, horizontal mount, 90 thru hole termination, tin/lead leadframe, 1.2 x .160 mounting screw w/ 2 standoffs, thread for 1.2 jackscrews.
8-1589681-6	1589602	STM03711309M6DQ	Dualobe, 2 row, metal, 37 position, special 11309, receptacle, horizontal mount, 90 thru hole termination, tin/lead leadframe, 1.2 x .160 mounting screw w/ 2 standoffs, thread for 1.2 jackscrews.
2-1589682-0	1589602	STM05111015M6SN	Dualobe, 2 row, metal, 51 position, special 11015, receptacle, horizontal mount, 90 thru hole termination, .125 long, tin/lead leadframe, 1.0 x .160 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
2-1589682-8	1589602	STM05111309M6DQ	Dualobe, 2 row, metal, 51 position, special 11309, receptacle, horizontal mount, 90 thru hole termination, .125 long, tin/lead leadframe, 1.2 x .160 mounting screw w/ 2 standoffs, thread for 1.2 jackscrews.