

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Jumper Bars

General Information

Extended Product Type:	BJM62
Product ID:	1SNA174112R1600
EAN:	3472591741124
Catalog Description:	BJM62-6 Jumper Bars
Long Description:	- Assembled screw jumper bars, - Perforated jumper bar with captive screws and spacers, - Allows the connection of consecutive blocks or not: remove unnecessary screw and spacer.

Ordering

Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC160001C0207-CH-J Accessories
Instructions and Manuals:	1SNC160001C0207-CH-J Accessories

Dimensions

Product Net Weight:	6 g
----------------------------	-----

Technical

Spacing:	6 mm
Function:	Jumper Bars
Rated Current (I_n):	Main Circuit 32 A
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

Suitable For:	D4/6.A.LL
	D4/6.A.NLP
	D4/6.A.NTLP
	D4/6.L
	D4/6.LL
	D4/6.LLP
	D4/6.LNTP
	D4/6.NL
	D4/6.NLP
	D4/6.NTLP
	D4/6.T
	D4/6.T3.P
	DR4/6
	DR4/6.1
	DR4/6.G

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225001C1009
Instructions and Manuals:	1SNC160001C0207-CH-J Accessories

Classifications

Object Classification Code:	X
ETIM 4:	EC000489 - Cross-connector for terminal block
ETIM 5:	EC000489 - Cross-connector for terminal block
ETIM 6:	EC000489 - Cross-connector for terminal block

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	125 mm
Package Level 1 Depth / Length:	170 mm
Package Level 1 Height:	5 mm
Package Level 1 Gross Weight:	0.06 kg
Package Level 1 EAN:	3472591741124
Package Level 2 Units:	800 piece
Package Level 2 Width:	175 mm
Package Level 2 Depth / Length:	227 mm
Package Level 2 Height:	130 mm
Package Level 3 Units:	144000 piece
Product Packing Type:	Bag

