

# MC812PA 101->200 Vertical



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Markers and Marking Systems  
→ Terminal Block Markers

## General Information

<b>Extended Product Type:</b>	MC812PA 101->200 Vertical
<b>Product ID:</b>	1SNK165022R0000
<b>EAN:</b>	3472591650228
<b>Catalog Description:</b>	MC812PA Terminal Block Markers pre-printed : 101->200 Vertical
<b>Long Description:</b>	MC812PA Terminal Block Markers pre-printed : 101->200 Vertical.

## Ordering

<b>Color:</b>	White
<b>Minimum Order Quantity:</b>	1 piece
<b>Customs Tariff Number:</b>	39269097

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNK160011D0201
<b>Instructions and Manuals:</b>	1SNK160027C0201

## Dimensions

<b>Product Net Width:</b>	8 mm
<b>Product Net Height:</b>	12 mm
<b>Product Net Length:</b>	7.6 mm
<b>Product Net Depth / Length:</b>	7.6 mm
<b>Product Net Weight:</b>	14 g

## Technical

<b>Spacing:</b>	8 mm
<b>Function:</b>	Pre-printed marker card
<b>Insulation Material:</b>	Polyamide

## Technical UL/CSA

<b>Flammability According to UL94:</b>	V2
--	----

## Environmental

<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C Storage -55 ... +110 °C
<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment

## Certificates and Declarations (Document Number)

<b>Declaration of Conformity - CE:</b>	1SND225156C1000
<b>Environmental Information:</b>	1SND220060E1000
<b>Instructions and Manuals:</b>	1SNK160027C0201
<b>RoHS Information:</b>	1SND230504F0204

## Classifications

<b>Object Classification Code:</b>	X
<b>E-nummer:</b>	2967831
<b>ETIM 4:</b>	EC000761 - Labelling for terminal block
<b>ETIM 5:</b>	EC000761 - Labelling for terminal block
<b>ETIM 6:</b>	EC000761 - Labelling for terminal block

## Container Information

<b>Package Level 1 Units:</b>	1 piece
<b>Package Level 1 Width:</b>	120 mm
<b>Package Level 1 Depth / Length:</b>	200 mm
<b>Package Level 1 Gross Weight:</b>	0.014 kg
<b>Package Level 1 EAN:</b>	3472591650228
<b>Package Level 2 Units:</b>	400 piece
<b>Package Level 3 Units:</b>	9600 piece

