

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Jumper Bars

General Information

Extended Product Type:	JB10-2
Product ID:	1SNK910302R0000
EAN:	3472599097728
Catalog Description:	JB10-2 Jumper Bar - Orange
Long Description:	Facilitate & secure your jumper bar assembly process: - Screwless mounting, - Pre-cut poles for alternated jumpering between terminal blocks, - Insulated, - Positive locking, - Perfectly adapted to low level electrical contact (20mA, 50mV).

Ordering

Color:	Orange
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNK160031D0201
Instructions and Manuals:	1SNK160027C0201

Dimensions

Product Net Width:	10 mm
Product Net Height:	18.5 mm
Product Net Length:	31.5 mm
Product Net Depth / Length:	31.5 mm
Product Net Weight:	4.6 g

Technical

Spacing:	10 mm
Function:	Jumper Bars
Rated Current (I_n):	Main Circuit 76 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 1920 A
Rated Voltage (U_r):	1000 V
Rated Impulse Withstand Voltage (U_{imp}):	6000 V
Dielectric Test Voltage:	2200 V

Pollution Degree:	3
Power Loss:	2.4 W
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Suitable For:	ZK10 ZK10-3P ZK10-PE ZK10-PE-3P ZS16 ZS16-PE

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Flammability According to UL94:	V0

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

ATEX Certificate:	1SND162004A1708
CB Certificate:	1SND161021A0201
Instructions and Manuals:	1SNK160027C0201
RoHS Information:	1SND230499F0202

Classifications

Object Classification Code:	X
E-nummer:	2925383
ETIM 4:	EC000489 - Cross-connector for terminal block
ETIM 5:	EC000489 - Cross-connector for terminal block
ETIM 6:	EC000489 - Cross-connector for terminal block

Container Information

Package Level 1 Units:	50 piece
Package Level 1 Width:	50 mm
Package Level 1 Depth / Length:	117 mm
Package Level 1 Height:	50 mm
Package Level 1 Gross Weight:	0.23 kg

Package Level 1 EAN: 3472599097728

Package Level 2 Units: 1500 piece

Package Level 3 Units: 144000 piece

