

JB22-10



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Jumper Bars

General Information

Extended Product Type:	JB22-10
Product ID:	1SNK922310R0000
EAN:	3472599163638
Catalog Description:	JB22-10 Jumper Bar
Long Description:	Screw jumper bars

Ordering

Minimum Order Quantity:	5 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNK160033D0201
Instructions and Manuals:	1SNK160027C0201

Dimensions

Product Net Width:	22 mm
Product Net Height:	211 mm
Product Net Length:	20.7 mm
Product Net Depth / Length:	20.7 mm
Product Net Weight:	157.4 g

Technical

Spacing:	22 mm
Function:	Jumper Bars
Rated Current (I_n):	Main Circuit 192 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 8400 A
Rated Voltage (U_r):	1000 V
Rated Impulse Withstand Voltage (U_{imp}):	8000 V
Dielectric Test Voltage:	2200 V
Power Loss:	6.1 W
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide

Recommended Screw Driver: 4 mm

Suitable For: D70/22
ZS70

Technical UL/CSA

**Maximum Operating Voltage
UL/CSA:** Main Circuit 600 V

Environmental

Ambient Air Temperature: Operation -55 ... +110 °C
Storage -55 ... +110 °C

RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

ATEX Certificate: 1SND162004A1708

CB Certificate: 1SND161034A0202

Instructions and Manuals: 1SNK160027C0201

RoHS Information: 1SND230499F0202

Classifications

Object Classification Code: X

E-number: 2925396

ETIM 4: EC000489 - Cross-connector for terminal block

ETIM 5: EC000489 - Cross-connector for terminal block

ETIM 6: EC000489 - Cross-connector for terminal block

Container Information

Package Level 1 Units: 5 piece

Package Level 1 Width: 54 mm

Package Level 1 Depth / Length: 252 mm

Package Level 1 Height: 52 mm

Package Level 1 Gross Weight: 0.787 kg

Package Level 1 EAN: 3472599163638

Package Level 2 Units: 45 piece

Package Level 2 Width: 200 mm

Package Level 2 Depth / Length: 300 mm

Package Level 2 Height: 200 mm

Package Level 2 Gross Weight: 7.36 kg

Package Level 3 Units: 4320 piece

Product Packing Type: Box

