


PE457-6 Economy Yagi Antennas

ECONOMY P AND PE SERIES

Where economy is important, these Yagis are your best choice. Aluminum 3/16 inch (.5 cm) rod elements and 7/8 inch (2.2 cm) booms are standard with economy Yagis. The PE457-6 features insulated, through-the-boom element mounting. The P406-3 and P457-3 6dB models have the elements mounted on the side of the boom.

FEATURES

- Solid aluminum elements
- Heavy-walled booms
- Stackable for more gain
- Broadband



PARAMETER	SPECIFICATIONS			
Model Number	p406-3	p457-3	pE457-6	p4495-4
Frequency (MHz)	406-430	450 - 470	450 - 470	440 - 495
Gain (dBd)	6.0	6.0	8.2	6.5
Number element	3	3	6	4
Front-to-back (dB)	18	18	12	15
E-Plane (3dB beamwidth)	65°	65°	50°	65°
H-Plane (3dB beamwidth)	100°	100°	59°	80°
Connector Type (f)	UHF	UHF	UHF	UHF
W/ surface area ft2 (m2)	0.1 (0.01)	0.1 (0.01)	0.3 (0.028)	0.15 (0.015)

PARAMETER	SPECIFICATIONS			
W/ survival mph (kph)	125 (200)	125 (200)	125 (200)	125 (200)
W/ 1/2" Ice	94 (125)	94 (125)	100 (161)	94 (125)
Length in (cm)	15.25 (39.0)	15.25 (39.0)	36 (91.0)	22 (55.9)
Weight lb (kg)	1.5 (0.68)	1.5 (0.68)	2.4 (1.1)	1.7 (.76)

TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

te.com

TE, and TE connectivity (logo) are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

TE Connectivity warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations TE Connectivity will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the TE Connectivity product is installed. Useful lifetime of the original end product may vary but is not warranted to exceed one (1) year from the original date of the end product purchase.

©2022 TE Connectivity. All Rights Reserved.

08/22 Original