




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION .19
 © COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.



LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
-	-	B	REVISED ECR-10-002174	5FEB10	LYM	LSF	



- NOTES:
- 1 MATERIAL: GLASS FILLED HIGH TEMP NYLON, NATURAL COLOR (BEIGE)
 HOUSING: PHOSPHOR BRONZE
 CONTACT: BRASS
 SOLDER PEG : BRASS
 - 2 FINISH: MATTE TIN OVER NICKEL UNDERPLATE
 - 3. PACKING: TAPE & REEL (PACKAGING SPEC: 107-51189)




SECTION A-A
SCALE 10:1



SCALE 10 : 1

H	G	F	E	POS.	PART NO.
29.00	33.00	31.00	31.00	30	3-1735360-0
28.00	33.00	30.00	30.00	29	2- -9
27.00	31.00	29.00	29.00	28	2- -8
26.00	30.00	28.00	28.00	27	2- -7
25.00	29.00	27.00	27.00	26	2- -6
24.00	28.00	26.00	26.00	25	2- -5
23.00	27.00	25.00	25.00	24	2- -4
22.00	26.00	24.00	24.00	23	2- -3
21.00	25.00	23.00	23.00	22	2- -2
20.00	24.00	22.00	22.00	21	2- -1
19.00	23.00	21.00	21.00	20	2-1735360-0
18.00	22.00	20.00	20.00	19	1- -9
17.00	21.00	19.00	19.00	18	1- -8
16.00	20.00	18.00	18.00	17	1- -7
15.00	19.00	17.00	17.00	16	1- -6
14.00	18.00	16.00	16.00	15	1- -5
13.00	17.00	15.00	15.00	14	1- -4
12.00	16.00	14.00	14.00	13	1- -3
11.00	15.00	13.00	13.00	12	1- -2
10.00	14.00	12.00	12.00	11	1- -1
9.00	13.00	11.00	11.00	10	1-1735360-0
8.00	12.00	10.00	10.00	9	-9
7.00	11.00	9.00	9.00	8	-8
6.00	10.00	8.00	8.00	7	-7
5.00	9.00	7.00	7.00	6	-6
4.00	8.00	6.00	6.00	5	-5
3.00	7.00	5.00	5.00	4	1735360-4



THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DWN KT GOH 05MAY2006
 CHK WL CHOO
 APVD WL CHOO
 PRODUCT SPEC -
 APPLICATION SPEC -
 WEIGHT -

Tyco Electronics Corporation
 Singapore

NAME ASSY, 1.00mm FFC CONN, SMT, H, (NON-ZIF), BOTTOM CONTACT

SIZE A3 CAGE CODE 00779 DRAWING NO C-1735360

CUSTOMER DRAWING SCALE 5 SHEET 1 OF 1 REV B