



Modular Jacks

Virtual Sample Kit

With one click on the part number you can:

- View Product Details

With a second click you can:

- Request samples
- View product drawing or related specifications
- View 3D pdf
- Check pricing & availability

www.te.com/products/modjacks


Stacked 8 & 2 Position, Shielded, Right Angle

Part Number	Description
6116151-1	2x1 Over Stacked USB Receptacle, with and without LED, PCB Ground, Cat 3
1888653-7	2x1 Panel and PCB Ground, Offset, LED, Cat 5e
1888653-1	2x1 Panel and PCB Ground, Offset Cat 5e
1888652-1	2x1 Panel and PCB Ground, 2 Pos., Offset, Cat 5e
6368035-1	2x6 with LED, Offset, Panel and PCB Ground, Cat 5e
6116317-1	2x8 PCB and Panel Ground, with LED, Cat 5e



Stacked 8 Position, Shielded, Right Angle

Part Number	Description
5569381-1	2x1 Panel Ground, Cat 5
5569255-1	2x2 PCB Ground, Cat 5
5569256-1	2x3 PCB Ground, Cat 5
5569257-1	2x4 PCB Ground, Cat 5
5406494-1	2x6 PCB and Panel Ground, Cat 5
5569264-1	2x8 Panel and PCB Ground, Cat 5



1x1 Single Port, 8 Position

Part Number	Description
5406436-1	Vertical Shielded with Panel Stops, PCB and Panel Ground, Cat 3
5555162-1	Right Angle, Low Profile, with Panel Stops, Cat 3
5558342-1	Right Angle Low Profile, Shielded, PCB Board Grounded, Cat 5e
6116201-1	Vertical, Compliant Pin, Cat 5
1-406541-1	Right Angle, Shielded, Panel and PCB Ground, Cat 5
215877-1	Right Angle for PCB, Cat 3
1888250-3	Low Profile, Press Fit, Panel and PCB Ground, Cat 5

1x1 Single Port, Right Angle, 8 Position

Part Number	Description
6339191-1	Shielded, Surface Mount, Panel and PCB Ground, Cat 5
2-406549-4	Shielded, Panel Ground, LED, Cat 5
1116062-2	Shielded, 10mm Panel and PCB Ground, Cat 5
5558343-1	Unshielded, Low Profile, Surface Mount with Panel Stops, Cat 5e



Multiple Port, Right Angle, 8 Position

Part Number	Description
1888251-1	Low Profile 1x4 Press Fit, Panel and PCB Ground, Shielded, Cat 5
6116353-1	Inverted 1x2 Shielded, Panel Ground with LED, Cat 5
6339169-3	1x8 Shielded Wave Panel Ground Cat 5
5557564-1	1x6 Unshielded Cat 3



RJ Point Five Connector, 8 Contacts, Right Angle

Part Number	Description
2170129-1	Multiple Port 1x2 Offset, Cat 5e
2057133-1	Stacked 2x8, Cat 5e
2057134-1	Stacked 2x12, Cat 5e

