






REVISIONS				
P.	LTN	DESCRIPTION	DATE	APVD
B		REVISED PER ECR-20-100642	23SEP2022	M, G, D, Z



- NOTES:
- APPLICABLE CONTACT P/N:
 TAB CONTACT: 175150-□ (20-16 AWG)
 175149-□ (26-22 AWG)
 - MATING CONN. P/N:
 PLUG HSG: 176279-□
 REC HSG: 175152-□ (20-16 AWG)
 175151-□ (26-22 AWG)
 - INSTRUCTION SHEET: IS-503J.
 - APPLICABLE PANEL THICKNESS : 0.8-2.0 (SEE FIG 1)
 - INSERT CONN. FROM PRESS DIRECTION SIDE FOR METAL PANEL.
 - EDGE OF THICKNESS WAY MUST NOT ROUND FOR MOLDED PANEL.

DISCONTINUED	BLACK	15	176300-9
DISCONTINUED	BLUE	15	176300-6
DISCONTINUED	YELLOW	15	176300-4
DISCONTINUED	RED	15	176300-2
	NATURAL	15	176300-1
	HOUSING COLOR	POSITION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: Y. NARISAWA 25APR1990	TE Connectivity	
DIMENSIONS: mm		CHK: Y. FUJITA 19NOV1990	AMP UNIVERSAL POWER CONN, 3.96mm PITCH CAP HOUSING 15 Pos (PANEL MOUNT)	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: N. CHUQUE 20NOV1990	NAME	
0 PLC	±	PRODUCT SPEC	SIZE	
2 PLC	±0.25	108-5302	CAGE CODE	
3 PLC	±0.2	APPLICATION SPEC	DRAWING NO	
4 PLC	±	114-5142	RESTRICTED TO	
ANGLES	±°	WEIGHT	A 00779 ©=176300	
FINISH	-	CUSTOMER DRAWING	SCALE 5:1 SHEET 1 OF 1 REV B	
MATERIAL: 6/6 NYLON (UL 94 V-0)				