













THIS DRAWING IS A CONTROLLED DOCUMENT. FILE NO 1583005

TOOL NUMBER 	WIRE SIZE mm ² [AWG] 	INSULATION DIAMETER mm [in.] 	INSULATION ADJUSTER 	FLIP LOCATOR 	STRIP LENGTH mm [in.] 	CRIMP HEIGHT mm [in.] 	CONTACT PART NUMBERS 		CONTACT DESCRIPTION	APPLIC. SPECIFIC.		
							LOOSE PIECE 	STRIP FORM 				
91509-1 91509-3	0.50-0.89 [20-18] 1.25-1.42 [16]	2.29-3.30 [.090-.130]	YES	NO	4.75 ± 0.38 [.187 ± .015]	1.27 ± 0.05 [.050 ± .002] 1.52 ± 0.08 [.060 ± .003]	42566-[] 60196-3 62228-1 42638-2	62228-1	42452-[] 60196-[] 62026-1 60214-[] 60621-1	61084-1 61758-[] 61919-1 61939-1 62137-[]	187 FASTON Contacts	114-2036 and 114-35000
91511-1 91511-3	0.20-0.38 [24-22] 0.32-0.96 [22-18]	1.02-1.52 [.040-.060] 1.52-2.54 [.060-.100]	NO	NO	4.75 ± 0.38 [.187 ± .015]	0.76 ± 0.05 [.030 ± .002] 1.14 ± 0.05 [.045 ± .002]	- 42922-[]	-	42067-[] 42415-[] 42635-[]	-	110 FASTON Contacts	114-2036 and 114-35000
91514-1 91514-3	0.32-0.96 [22-18]	1.52-2.54 [.060-.100] 2.29-3.30 [.090-.130]	YES	NO	6.35 ± 0.38 [.250 ± .015]	1.40 ± 0.10 [.055 ± .004]	41969-[] 42731-[] 60878-2 61316-1 170187-[] 170095-1	-	41772-[] 42640-[] 60294-2 170183-[]	-	250 FASTON contacts	114-2036 and 114-35000
91581-1 91581-3	0.50-0.85 [20-18]	2.03-3.05 [.080-.120]	NO	NO	4.5 ± 0.38 [.177 ± .015]	0.97-1.10 [.038-.043] 1.42-1.55 [.056-.061]	170042-[] 172799-[] 170041-[]	-	170015-[] 170033-[] 170014-[]	-	110 FASTON Contacts	114-2036 and 114-35000
91593-1 91593-3	0.51-0.89 [20-18] 1.25-1.38 [16]	1.90-3.00 [.075-.118] 2.40-3.40 [.094-.134]	YES	NO	4.50 ± 0.50 [.177 ± .020]	1.10-1.24 [.043-.049] 1.35-1.54 [.053-.061]	170331-[]	-	170325-[]	-	187 POSITIVE LOCK FASTON Contacts	114-5041
2031929-1 2031929-3	0.32-0.96 [22-18]	1.52-2.54 [.060-.100]	NO	NO	4.75 ± 0.38 [.187 ± .015]	1.14 ± 0.05 [.045 ± .002]	42470-[]	-	42068-[]	-	110 FASTON Contacts	114-2036 and 114-35000
2063247-1 2063247-3	0.31-0.56 (22-20) 0.76-0.89 (18)	2.03-2.65 (.080-.104) 2.13-3.05 (.084-.120)	YES	NO	4.78 ± 0.38 (.188 ± .015)	1.37 ± 0.05 (.054 ± .002) 1.57 ± 0.05 (.062 ± .002)	-	-	42490-[]	-	187 FASTON Contacts	114-2036
2063846-1 2063846-3	0.20-0.38 [24-22] 0.32-0.96 [22-18]	1.02-1.52 [.040-.060] 1.52-2.54 [.060-.100]	NO	NO	4.75 ± 0.38 [.187 ± .015]	0.76 ± 0.05 [.030 ± .002] 1.14 ± 0.05 [.045 ± .002]	61454-1 42470-[]	-	42067-[] 42415-[] 42068-[]	-	110 FASTON Contacts	114-2036 and 114-35000



 LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.

2. AMP, CERTI-CRIMP, and FASTON ARE TRADEMARKS.










 -1 IS A CERTICRIMP II HAND TOOL ASSEMBLY. -3 IS A CERTICRIMP II HEAD SUB-ASSEMBLY.

4. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414.

CERTI-CRIMP II DATA SHEET

DWN: M. YOUNGER 21FEB2012		MATERIAL: -		HEAT TREAT: -																
CHK: B.A.WOLFE 22FEB2012		APVD: B.A. WOLFE 22FEB2012		 TE Connectivity Ltd.																
NAME: B.A. WOLFE		SCALE: -																		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± -																
ANGLE: - SURFACE TEXTURE: 		REVISION RECORD: <table border="1"> <tr> <th>P</th> <th>LTR</th> <th>DATE</th> <th>DWN</th> <th>APVD</th> </tr> <tr> <td>E</td> <td>REVISED</td> <td>12JUL2022</td> <td>RRD</td> <td>CH</td> </tr> <tr> <td>D5</td> <td>REVISED</td> <td>11/2015</td> <td>AW</td> <td>BAW</td> </tr> </table>		P	LTR	DATE	DWN	APVD	E	REVISED	12JUL2022	RRD	CH	D5	REVISED	11/2015	AW	BAW	CERTI-CRIMP II TOOL DATA SHEET FASTON & POSITIVE LOCK CONTACT FAMILY DRAWING NO: 1583005	
P	LTR	DATE	DWN	APVD																
E	REVISED	12JUL2022	RRD	CH																
D5	REVISED	11/2015	AW	BAW																
SCALE: -		SIZE: A1		SHEET: 1 of 2																

THIS DRAWING IS A CONTROLLED DOCUMENT. FILE NO 1583005

TOOL NUMBER 	WIRE SIZE mm ² [AWG] 	INSULATION DIAMETER mm [in.] 	INSULATION ADJUSTER 	FLIP LOCATOR 	STRIP LENGTH mm [in.] 	CRIMP HEIGHT mm [in.] 	CONTACT PART NUMBERS [△]		CONTACT DESCRIPTION	APPLIC. SPECIF.
							LOOSE PIECE 	STRIP FORM 		
2063851-1	0.20-0.35 [24-22]	1.50-2.55 [.059-.100]	NO	NO	3.50 ± 0.50 [.138 ± .020]	0.89-0.99 [.035-.039]	170203-2	-	187 FASTON contacts	114-5013
	0.50-0.56 [20]	1.95-2.60 [.077-.102]				1.00-1.10 [.039-.043]				
2063760-1 2063760-3	0.20-0.35 [24-22]	1.50-1.90 [.059-.075]	NO	NO	4.5 ± 0.5 [.177 ± .020]	0.90-1.05 [.035-.041]	170330-()	170324-()	.187 SERIES POSITIVE LOCK RECEPTACLE	114-5041
	0.50-0.53 [20]	2.00-2.70 [.079-.106]				1.00-1.13 [.039-.047]				



[△] LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.

2. AMP, CERTI-CRIMP, and FASTON ARE TRADEMARKS.

[△] -1 IS A CERTICRIMP II HAND TOOL ASSEMBLY. -3 IS A CERTICRIMP II HEAD SUB-ASSEMBLY.

4. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414.

CERTI-CRIMP II DATA SHEET

DIN: M. YOUNGER 21FEB2012		MATERIAL: -		HEAT TREAT: -	
CHK: B.A. WOLFE 22FEB2012		APVD: B.A. WOLFE 22FEB2012			
NAME: B.A. WOLFE		SCALE: -			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SURFACE TEXTURE: 	
0 PLC ± -		1 PLC ± -		2 PLC ± -	
3 PLC ± -		4 PLC ± -		ANGLES: -	
P LTR		REVISION RECORD		DATE	
- SEE SHEET 1		-		-	
- SEE SHEET 1		-		-	
DIN		APVD		DRAWING NO: 1583005	
-		-		SHEET 2 OF 2	
-		-		REV E	

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY LTD. IT IS TO BE USED ONLY FOR THE PURPOSES AND BY THE PERSONNEL AUTHORIZED BY TE CONNECTIVITY LTD. WITHOUT AUTHORIZATION FROM TE (www.te.com)