







REVISIONS				
P.	LTN	DESCRIPTION	DATE	DWN APVD
I		PRELIMINARY	17OCT2014	DLD CJS
A		RELEASED PER ECO-15-002891	24FEB2015	DLD CJS
A1		REVISED PER ECO-18-013523	28AUG2018	JMS CS
A2		REVISED PER ECO-19-004164	25MAR2019	JMS CS







- △ TPA SHIPPED IN PRE-LATCHED POSITION.
- 2. 2288274-1 SHOWN IN GENERAL VIEWS.
- △ THIS PART NUMBER HAS NOT COMPLETED VALIDATION TESTING.
- △ PRELIMINARY - NOT RELEASED FOR PRODUCTION
- △ DUE TO BULK PACKAGED ARRANGEMENT, TPA MAY BE MOVED FROM THE PRE-LATCHED POSITION TO CLOSED OR PARTIALLY CLOSED DURING SHIPMENT. PLEASE REFER TO TE SPECIFICATION 408-32044 FOR TPA RESET INSTRUCTIONS.
- 6. APPLICABLE RECEPTACLES FOR THIS CONNECTOR:
 0.64 GENERATION Y - TE P/N'S 2035334-X AND 1924955-X
 2.8 CIRCUITS - FCI APEX 2.8 FAMILY, REF P/N 54001431 OR SIMILAR (ACCEPTS 10AWG - 22AWG)



PARTS MARKED WITH EITHER GF33 OR GF35

PARTS MARKED WITH EITHER GF33 OR GF35

OPTIONAL NON-FUNCTIONAL VOID CORING



KEY A

KEY B

KEY C

KEY D

KEYING ARRANGEMENT

△ 3/4	D	---	2288274-4
	C	BROWN	2288274-3
	B	GRAY	2288274-2
	A	BLACK	2288274-1
	KEYING OPTION	COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	D. DRUMMOND	17OCT2014
DIMENSIONS:		CHK	C. SCHMID	17OCT2014
mm	0 PLC ±	APVD	C. SCHMID	17OCT2014
	1 PLC ±0.3	NAME		
	2 PLC ±	PLUG ASSEMBLY,		
	3 PLC ±	24 POSITION UNSEALED HYBRID		
	4 PLC ±	(4X 2.8, 20X 0.64)		
	ANGLES ±	SIZE CAGE CODE DRAWING NO RESTRICTED TO		
	FINISH ±	408-32044		
MATERIAL		WEIGHT	A100779C=2288274	
			Customer Drawing	
		SCALE	4:1	SHEET 1 OF 1 REV A2