



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
010	RELEASED	8/23/85	R.GIERAS
021	CHANGED PICTORIALY, ECN 86-0436-6	MB 6/2/86	R.GIERAS
020	M39012/83B3003 WAS M39012/83-3003, ECN 87-0029	BA 7/20/87	JB 7/24/87
030	REDESIGNED, ECN 89-0562-1	KCM 6/7/89	<i>IComet</i>

	DIM 'A'
BEFORE CRIMPING	.765 REF (19.4 mm)
AFTER CRIMPING	.655 MAX (16.6 mm)

COMPONENT	MATERIAL	FINISH
HOUSING MOUNTING NUT BUSHING LOCKWASHER	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	PASSIVATE PER ASTM-A380
DIELECTRIC	TFE FLUOROCARBON PER MIL-P-19468 AND FED SPEC L-P-403 AND ASTM-D-1457	N/A
CENTER CONTACT	BERYLLIUM COPPER PER QQ-C-530, ALLOY 173	GOLD PLATE PER MIL-G-45204 OVER COPPER PLATE PER MIL-C-14550
O-RING	SILICONE RUBBER PER ZZ-R-765	N/A

NOTES:

- DESIGNED FOR USE WITH .085 DIA SEMI-RIGID CABLE
- CAPTURED CENTER CONTACT
- PICTORIAL VIEW IS AFTER CRIMPING
- MIN STRAIGHT CABLE LENGTH .341
- IT IS SUGGEST TO BEND CABLE PRIOR TO CRIMPING

CABLE ENTRY DIAMETER MINIMUM	
HOUSING	.088
CONTACT	.021

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES
TOLERANCE ON
FRAC. DEC. ANGLES
±.005 ± °

These drawings and specifications are the property of Omni Spectra Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of items without written permission.

DESIGNED BY J.M.P. 8/21/85
CHECKED BY R.RUSSO 8/23/85
APPROVED BY R.RUSSO 8/23/85

USE ASSY PROCEDURE

NO. A.P. 20-570

Omni Spectra Omni Spectra, Inc.
Microwave Connector Division

TITLE OSM BULKHEAD FEEDTHRU CABLE JACK - COMPRESSION CRIMP M39012/83B3003 CAT 'B'

SIZE B	CODE IDENT NO. 26805	2004-8203-92	REV 030
--------	----------------------	--------------	---------

SCALE 6:1 SHEET 1 OF 1

CUSTOMER

1051030
SHEET 1 OF 1
REV 0