

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	REVISED PER ECR-17-009578	04JUL2017	BW	FV
	D2	REVISED PER ECO-18-015222	09JAN2019	DT	TD
	D3	REVISED PER ECR-20-012400	25SEP2020	SS	EW

1 REVERSE REELING
2 ONLY WELDED SPLICES ALLOWED

SECTION C-C

TOOL 13094

TOOL 13123

SECTION D-D

1	PRE-TIN	PHOS. BRONZE	142685-5
2	PRE-TIN	PHOS. BRONZE	142685-3
	FINISH	MATERIAL	PART NUMBER

WIRE AREA	0.35mm ² - 1mm ²
INSULATION DIAMETER	1.3 - 2±0.1
APPLICATION FEED	22±0.1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.3
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±5°MATERIAL
-FINISH
-

DWN	05JUL2017	BASVESH WARAD
CHK	05JUL2017	VIRIDIA, FEDERICO
APVD	05JUL2017	DING, TIM
PRODUCT SPEC	-	
APPLICATION SPEC	-	
WEIGHT	-	
CUSTOMER DRAWING		

		NAME	
		L.I.F POSITIVE LOCK 5MM SERIES	
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-142685	
SCALE		SHEET	REV
6:1		1 OF 1	D3

1470-19 (3/13)