





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS 変更					
J	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
		D1		REVISED PER ECR-15-012855	19OCT2015	NK	GJ



1 使用端子型番：172781,172782

2 一般公差：±0.4

1 APPLICABLE CONTACT: 172781,172782

2 GENERAL TOLERANCE: ±0.4

OBSOLETE	-15	30.8	12	24			1-	-5
	12	24.8	11	22			1-	-2
OBSOLETE	-10	20.8	9	18			1-	-0
OBSOLETE	-9	18.8	8	16				-9
	8	16.8	7	14				-8
	7	14.8	6	12				-7
	6	12.8	5	10				-6
	5	10.8	4	8				-5
	4	8.8	3	6				-4
	3	6.8	2	4				-3
	2	4.8	1	2	NATURAL (自然色)			172890-2
極数 POS	寸法 DIMENSION			A B C	色調 COLOR		型番 P/N	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.SATO	15NOV2007	<b>STE</b> TE Connectivity				
DIMENSIONS: 単位： 耗 mm		CHK S.MANABE	15NOV2007					
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD S.MANABE	15NOV2007	NAME 名称				
0 PLC ±		PRODUCT SPEC 製品規格		HEADER HOUSING				
1 PLC ±		108-5163		LOW PROFILE MINI AMP-IN, 2MM PITCH				
2 PLC ±		APPLICATION SPEC 取付適用規格		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO
3 PLC ±		114-5062		A3		00779	C-172890	-
4 PLC ±		WEIGHT		SCALE		SHEET	REV	
ANGLES ±		FINISH 仕上		10:1		1 OF 1	D1	
MATERIAL 材料		CUSTOMER DRAWING		66ナイロン (UL94V-0)				
				66NYLON (UL94V-0)				