



REVISIONS					
P	LTR	DESCRIPTION	DATE	DN	APVD
B8		REVISED PER ECR-23-193923	25MAR24	RK	CAS

- 1 THE NOTED DIMENSION APPLIES AT THE INTERSECTION OF THE POST AND HOUSING
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 3 OBSOLETE PART NUMBER
- 4 HOUSING: FLAME RETARDANT THERMOPLASTIC, COLOR-BLACK. POST: PHOSPHOR BRONZE.
- 5 .000030 MIN GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL.
- 6 .000030 MIN GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN ON SOLDER TAIL, ALL OVER .000050 NICKEL.
- 7 DELETED
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



SECTION X-X



6	2	NONE	-	.106	.332	.200	2	6	5-147432-4
6	2	2	-	.206	.532	.400	4	10	5-147432-1
5	5	NONE	1.106	.106	1.332	1.200	12	26	147432-3
5	NONE	4	1.306	.106	1.532	1.400	14	30	147432-2
5	2	2	-	.206	.532	.400	4	10	147432-1

PLATING	ROW N	ROW M	E	D	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES
 TOLERANCES UNLESS OTHERWISE SPECIFIED:
 0. PLC ± -
 1. PLC ± -
 2. PLC ± -
 3. PLC ± .005
 4. PLC ± -
 ANGLES ± -
 MATERIAL: SEE TABLE
 FINISH: SEE TABLE

CUSTOMER DRAWING
 SCALE: 4:1
 SHEET: 1 of 1
 REV: B8

HAYMAKER 14MAR00
 J. GESFORD 14MAR00
 J. GESFORD 14MAR00
 NAME: HDR ASSY, MOD II, SHRD
 PRODUCT SPEC: 4 SIDES, DR, .100X.100
 APPLICATION SPEC: RA, W/ .025 SQ POSTS, SELECT LOADS
 SIZE: A1
 CAGE CODE: 00779
 DRAWING NO: 147432
 WEIGHT: -
 RESTRICTED TO: -

STE TE Connectivity